



DESCRIPTION: M5 MALE - CABLE MOUNT - SOLDER CUP - 3 POSITION

SPECIFICATIONS:

**MATERIALS:**  
HOUSING: TPU, BLACK  
CONTACTS: GOLD PLATED BRASS  
(SEE P/N KEY BELOW)  
NUT: (SEE P/N KEY BELOW)


**ELECTRICAL:**  
RATED CURRENT: 1A  
RATED VOLTAGE: 60V  
INSULATION RESISTANCE: 100 MOhms MIN.  
CONTACT RESISTANCE: 10 mOhms MAX.

**ENVIRONMENT:**  
OPERATING TEMPERATURE: -40°C TO +85°C  
WATER PROOF: IP67  
MAX WIRE AWG: 28





850-003-103RLUY

1 = GOLD FLASH  
4 = 10u" GOLD  
3 = NICKEL PLATED BRASS NUT  
S = STAINLESS STEEL NUT



NUT



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:  
M. SIGMON

DATE:  
03/04/2016

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING

NorComp

SCALE:  
NTS

SHEET 1 OF 1

REV 7

DWG NO.

850-003-103RLUY