

DESCRIPTION: M5 FEMALE - CABLE MOUNT - SOLDER CUP - 3 POSITION

SPECIFICATIONS:

MATERIALS:

HOUSING:	TPU, BLACK
CONTACTS:	GOLD PLATED BRASS (SEE P/N KEY BELOW)
NUT:	(SEE P/N KEY BELOW)
ORING:	NBR, BLACK



ELECTRICAL:

RATED CURRENT:	1A
RATED VOLTAGE:	60V
INSULATION RESISTANCE:	100 MOhms MIN.
CONTACT RESISTANCE:	10 mOhms MAX.


ENVIRONMENT:

OPERATING TEMPERATURE:	-40°C TO +85°C
WATER PROOF:	IP67

MAX WIRE AWG: 28




NUT



850-003-203RLUY

1 = GOLD FLASH
4 = 10μ" GOLD

3 = NICKEL PLATED BRASS NUT
S = STAINLESS STEEL NUT



UNITS = inch [mm]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
M. SIGMON

DATE:
03/03/2016

NorComp

SCALE:
NTS

SHEET 1 OF 1

REV
10

DWG NO.

850-003-203RLUY