


NOTE:

MATERIAL	
HOUSING:	PA66 UL94V-0, BLACK
CONTACT:	BRASS
NUT:	BRASS
SHELL:	BRASS
ORING:	NBR
GROUND:	PHOSPHOR BRONZE
FINISH	
CONTACT:	10u" GOLD PLATED OVER NICKEL
NUT:	NICKEL
SHELL:	NICKEL
GROUND:	BRIGHT TIN
ELECTRICAL	
RATED CURRENT:	1.5A(5/6P) / 3A(3/4P)
RATED VOLTAGE:	30V(5/6P) / 60V(3/4P)
INSULATION RESISTANCE:	100 MΩhms MIN.
CONTACT RESISTANCE:	10 mΩhms MAX.
WATER PROOF:	IP67
ENVIRONMENT	
OPERATION TEMPERATURE:	-40°C TO +85°C



857-YYY-213R004

003 = 3 POSITION
004 = 4 POSITION
005 = 5 POSITION
006 = 6 POSITION

*Key not required on mating connector.
NorComp M8 5P & 6P male mates do not
have key.

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
J. KADEL

DATE:
06/21/2021

UNITS = mm

NorComp

DO NOT SCALE FROM DRAWING

SCALE:
NTS

SHEET OF
1 2

REV
3

DWG NO.

857-YYY-213R004

