



DESCRIPTION: M12; 5 POS; FEMALE; B CODE; CABLE MOUNT



NUT

NOTE:

MATERIAL

HOUSING:

PBT UL94V-0, BLACK

CONTACT:

BRASS

SHELL:

BRASS

NUT:

BRASS

O-RING:

EPDM, BLACK

FINISH

CONTACT:

10u" GOLD PLATED

UNDER PLATE:

NICKEL

NUT:

NICKEL

SHELL:

NICKEL

ELECTRICAL

RATED CURRENT:

4A

RATED VOLTAGE:

60V

INSULATOR RESISTANCE:

100 MΩhms MIN.

CONTACT RESISTANCE:

10 mΩhms MAX.

WATER PROOF:

IP67

ENVIRONMENT

OPERATION TEMPERATURE:

-40°C TO +85°C

MAX WIRE AWG:

22

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

J. KADEL

DATE:

09/27/2019

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE:

NTS

SHEET

OF

1

1

REV

3

DWG NO.

858-B05-203RLS4