




DESCRIPTION: M12 // F // 3P SCODE // SOLDER CUP // CABLE MOUNT // UNSHIELDED

SPECIFICATIONS:


MATERIALS:
 HOUSING: PA66, UL94 V-0, BLACK
 CONTACTS: 10µ" GOLD PLATED BRASS
 NUT: NICKEL PLATED BRASS
 ORING: EPDM

ELECTRICAL:
 RATED CURRENT: 12A
 RATED VOLTAGE: 630V
 INSULATION RESISTANCE: 100 MOhms MIN.
 CONTACT RESISTANCE: 10 mOhms MAX.

ENVIRONMENT:
 OPERATING TEMPERATURE: -40°C TO +105°C
 WATER PROOF: IP67
 MAX WIRE AWG: 18 AWG



NUT



RoHS COMPLIANT

UNITS = mm

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: J. KADEL
 DATE: 12/11/2023

NorComp

SCALE: NTS	SHEET 1 OF 1	REV 0
DWG NO. 858-SP3-203RLU4		