

NOTE:

MATERIAL

Housing: PBT UL94V-0, BLACK
 Contact: BRASS
 Shell: BRASS
 Nut: BRASS
 O-Ring: EPDM, BLACK

FINISH



Contact: 10u" GOLD PLATED
 Under Plate: NICKEL
 Nut: NICKEL
 Shell: NICKEL

ELECTRICAL

Rated Current: 4A
 Rated Voltage: 60V
 Insulator Resistance: 100 MΩms MIN.
 Contact Resistance: 10 mΩms MAX.
 Water Proof: IP67

ENVIRONMENT

Operating Temp.: -40°C TO +85°C



Recommended Panel Cut-Out

RoHS COMPLIANT

UNITS = mm

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

A. Joyner

DATE:

10/30/2020

Tolerance

.X ±0.20

.XX ±0.10

.XXX ±0.05

NorComp

SCALE:

NTS

SHEET

OF

1

1

REV

3

DWG NO.

859-B05-203R004