

**SPECIFICATIONS:**

**MATERIALS:**


HOUSING: PA9T, UL94 V-0, BLACK  
 CONTACTS: GOLD FLASH PLATED BRASS  
 GROUND: NICKEL PLATED PHOSPHOR BRONZE  
 ORING: VITON  
 CAP: PA66

**ELECTRICAL:**



RATED CURRENT: 4A  
 RATED VOLTAGE: 250V  
 INSULATION RESISTANCE: 100 MOhms MIN.  
 CONTACT RESISTANCE: 10 mOhms MAX.

**ENVIRONMENT:**

OPERATING TEMPERATURE: -40°C TO +85°C  
 WATER PROOF: IP67 (Mated Condition)



**MUST PURCHASE PART NUMBER "862-M-SHELL" SEPARATELY**



**RoHS COMPLIANT**

UNITS = mm

**DO NOT SCALE FROM DRAWING**



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

J. KADEL

DATE:

03/18/2024

**NorComp**

SCALE:

NTS

SHEET

OF

1


2

REV

0

DWG NO.

**862-D04-113R001**



The tape size complies with the (EIA-481-D) specification requirements.

RoHS COMPLIANT

UNITS = mm

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

J. KADEL

DATE:

03/18/2024

NorComp

SCALE:

NTS

SHEET

OF

2

2

REV

0

DWG NO.

862-D04-113R001