

DESCRIPTION: B SIZE CIRCULAR // FEMALE CABLE KIT // BAYONET

| POSITIONS AVAILABLE |                         |  |              |              |
|---------------------|-------------------------|--|--------------|--------------|
| NorComp Part Number | POSITIONS (MATING VIEW) |  | MAX AMPERAGE | MAX WIRE AWG |
| 868-02A-203KIT      | 2A                      |  | 10A          | 18AWG        |
| 868-03A-203KIT      | 3A                      |  | 10A          | 18AWG        |
| 868-04A-203KIT      | 4A                      |  | 10A          | 18AWG        |
| 868-02B-203KIT      | 2B                      |  | 5A           | 24AWG        |
| 868-03B-203KIT      | 3B                      |  | 5A           | 24AWG        |
| 868-04B-203KIT      | 4B                      |  | 5A           | 24AWG        |
| 868-005-203KIT      | 5                       |  | 5A           | 24AWG        |
| 868-006-203KIT      | 6                       |  | 5A           | 24AWG        |
| 868-007-203KIT      | 7                       |  | 5A           | 24AWG        |
| 868-008-203KIT      | 8                       |  | 5A           | 24AWG        |
| 868-010-203KIT      | 10                      |  | 2A           | 26AWG        |
| 868-012-203KIT      | 12                      |  | 2A           | 26AWG        |


NOTE: 2A, 3A, & 4A MUST MATE WITH CORRESPONDING A SIZES  
2B, 3B, & 4B MUST MATE WITH CORRESPONDING B SIZES

SPECIFICATIONS:

**MATERIALS:**  
HOUSING: PA66, UL94 V-0, BLACK  
CONTACTS: GOLD FLASH PLATED BRASS  
LOCK NUT: PA66, UL94 V-0, BLACK  
ORING & GASKET & SEAL: SILICONE  
CLAMP RING & SEALING NUT: PA66, UL94 V-0, BLACK

**ELECTRICAL:**  
RATED CURRENT: SEE TABLE TO LEFT  
RATED VOLTAGE: 250V  
INSULATION RESISTANCE: 100 MOhms MIN.  
CONTACT RESISTANCE: 10 mOhms MAX.

**ENVIRONMENT:**  
OPERATING TEMPERATURE: -40°C TO +105°C  
WATER PROOF: IP67



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: J. KADEL  
DATE: 06/17/2024

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS  
DWG NO. 868-YYY-203KIT

SHEET 1 OF 1  
REV 1