




DESCRIPTION: M16 // M // SOLDER CUP // REAR PANEL MOUNT // SHIELDED











POSITION CHART (MATING SIDE SHOWN)

SPECIFICATIONS:

MATERIALS:

HOUSING: PA66, UL94 V-0, BLACK

CONTACTS: **GOLD FLASH PLATED BRASS**

NUT: **NICKEL PLATED BRASS** SHELL: NICKEL PLATED BRASS

ORING: **EPDM**

ELECTRICAL:

7A (3,4,5B) // 5A (6,7A,7B,8) RATED CURRENT:

RATED VOLTAGE: 250V

INSULATION RESISTANCE: 100 MOhms MIN.

CONTACT RESISTANCE: 10 mOhms MAX.

ENVIRONMENT:

OPERATING TEMPERATURE: -40°C TO +85°C

WATER PROOF:

IP67

MAX WIRE AWG:

22 AWG

TORQUE:

0.7Nm to 1.5Nm

879-YYY-103R001

POSITIONS (SEE POSITION CHART)

003 = 3 POSITION

004 = 4 POSITION

05B = 5(B) POSITION

006 = 6 POSITION

07A = 7(A) POSITION

07B = 7(B) POSITION

008 = 8 POSITION

ROHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: J. KADEL

DATE:

09/05/2023

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE: SHEET NTS DWG NO.

879-YYY-103R001

1

OF

REV

3