


SPECIFICATIONS:

METALIZED PLASTIC:

MATERIAL: HIGH TEMPERATURE ABS  
PLATING: NICKEL OVER COPPER

PLASTIC:

MATERIAL: HIGH TEMPERATURE ABS  
COLOR: BLACK  
OPERATING TEMPERATURE: -55°C TO +125°C



BACKSHELL KIT INCLUDES:

- (2) BACKSHELL HALVES
- (2) 4-40 THUMBSCREWS
- (2) HOUSING SCREWS  
(RECOMMENDED TORQUE 26 IN-OZ)
- (1) METAL STRAIN RELIEF CLAMP
- (2) STRAIN RELIEF SCREWS  
(RECOMMENDED TORQUE 30 IN-OZ)

DIMENSIONS					
SIZE	A	B	C	D	E
009	31.50	24.99	31.01	15.19	8.51
015	40.01	33.32	35.00	15.19	8.51
025	53.49	47.04	38.00	15.19	11.00
037	70.00	63.50	40.01	15.19	11.00
050	67.49	61.00	40.01	18.21	11.99

973-YYY-YYYRYY1

SERIES \_\_\_\_\_  
POSITIONS \_\_\_\_\_  
009  
015  
025  
037  
050  
MATERIAL \_\_\_\_\_  
010 = PLASTIC  
020 = METALIZED PLASTIC  
COLOR \_\_\_\_\_  
01 = BLACK (ONLY FOR 010 OPTION ABOVE)  
12 = NICKEL OVER COPPER (ONLY FOR 020 OPTION ABOVE)  
PUT-UPS \_\_\_\_\_  
1 = KIT

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:  
P. JENKINS

DATE:  
07/15/2005

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE:  
NTS

SHEET 1 OF 1

REV 2

DWG NO. 973-YYY-0Y0RYY1