


- CONNECTOR 1 : 858-008-203RLS4, MOLDED STRAIGHT HOOD, COLOR BLACK
- CONNECTOR 2 : 858-008-203RLS4, MOLDED STRAIGHT HOOD, COLOR BLACK
- WIRE : 24AWG, 4 TWISTED PAIRS, UL2835, FOIL SHIELD, COLOR BLACK, 30V
- CABLE DIAMETER : 6.50mm±0.19
- PIN OUT :

### WIRING SCHEMATIC



CCA-000-MYYR211

01 = 1 METER  
02 = 2 METERS  
03 = 3 METERS  
05 = 5 METERS

\*\*SEE PAGE 3 FOR CABLE  
SPECIFICATIONS

RoHS COMPLIANT

UNITS = "as indicated"

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:  
M. SIGMON

DATE:  
04-21-15

NorComp


SCALE:  
NTS

SHEET  
1 OF  
3

REV  
6

DWG NO.

CCA-000-MYYR211



RoHS COMPLIANT

UNITS = mm

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:  
M. SIGMON

DATE:  
04-21-15

NorComp

SCALE:  
NTS



SHEET OF  
2 3

REV  
6

DWG NO. CCA-000-MYYR211

ELECTRICAL CHARACTERISTICS

VOLTAGE RATING : 30V  
TEMPERATURE RATING : 60°C  
SPARK TEST : AC-2000V/0.15 sec MIN.  
DIELECTRIC STRENGTH : AC-750V/1 sec MIN.  
INSULATION RESISTANCE : PE: DC-500V 15000 MΩHM/100M MIN. AT 20°C  
CONDUCTOR RESISTANCE : 24AWG - 93.2 ΩHM/KM MAX. AT 20°C




COLOR CODE

- 1. BROWN \* BROWN/WHITE
- 2. BLUE \* BLUE/WHITE
- 3. ORANGE \* ORANGE/WHITE
- 4. GREEN \* GREEN/WHITE

RoHS COMPLIANT

DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: M. SIGMON	DATE: 04-21-15	<b>NorComp</b>	SCALE: NTS	SHEET 3 OF 3	REV 6
					DWG NO.	CCA-000-MYYR211	