

SPECIFICATIONS:

**MATERIALS:** 

HOUSING: PBT, UL94 V-0

CONTACTS: **GOLD FLASH PLATED BRASS** 

SHELL: TIN PLATED STEEL

**ELECTRICAL:** 


3A RATED CURRENT: WORKING VOLTAGE: 250V

INSULATION RESISTANCE: 1000 MOhms MIN.

CONTACT RESISTANCE: 15 mOhms MAX.

ENVIRONMENT:

OPERATING TEMPERATURE: -55°C TO +105°C



RoHS



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: C. SMITH DATE: 10/12/2007

DO NOT SCALE FROM DRAWING

NorComp

SCALE: SHEET OF REV NTS 4 1 DWG NO. GCHDLP15F15F