


RJ45 FACE VIEW
BOTH ENDS



NOTES:

1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE
3. ELECTRICAL SPECIFICATIONS
VOLTAGE RATING: 30VAC
CURRENT RATING: 1.5 AMPS


CABLE P/N MATRIX

E66A06017MXXX

CONNECTOR TYPE
(DBL ENDED RJ45 PLUG TO RJ45 PLUG)

CABLE TYPE
(22 AWG 2PAIR PLTC)

FINISHED LENGTH
M001 = 0.1M
M010 = 1.0M
M100 = 10.0M



4	1	WRAP LABEL	VINYL	BLACK/YELLOW
3	1	RJ45 BOOT	PVC	BLACK
2	1	RJ45 PLUG	PC SHELL, BRASS CONT	CLEAR, GOLD PLT
1	1	CABLE, PROFINET, 2PR, 22 AWG, SHLD, PLTC	TPE JACKET	GREEN
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

RELEASED
EC NO: IPG2016-0528
DRAWN BY: RSTONE
CHKD BY: KJOZWIK
APPR: BWOODMAN
2015/10/08
2015/10/12

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± ---	± .01
1 PLACE	± 0.3	± ---
0 PLACE	± ---	± ---

ANGULAR ± 1°
DRAFT WHERE APPLICABLE
MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE
IN/MM

DRAWN BY	DATE
RSTONE	2015/10/08
CHECKED BY	DATE
KJOZWIK	
APPROVED BY	DATE
BWOODMAN	2015/10/12
MATERIAL NO.	
SIZE	
B	

SCALE 1:1
DESIGN UNITS INCH
THIRD ANGLE PROJECTION

RJ45 CABLE ASSY
RJ45 PLUG TO RJ45 PLUG
22 AWG, 2 PAIR PLTC

molex

DOCUMENT NO. SD-120108-093
SHEET NO. 1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION