



Views from "X" rotated


6-Pole




7-Pole




9-Pole
(8+1)




12-Pole




16-Pole



17-Pole




19-Pole
(16+3)



Cable Diameter		Solder Contacts	Crimp Contacts	Without Contacts
6 Pole		KRS6G20-553 1202310001	KRS6G20-403 1202310002	KRS6G20-003 1202310003
	Crimp range*		0,75-2,5mm ²	
7 Pole		KRS7G20-553 1202310004	KRS7G20-403 1202310005	KRS7G20-003 1202310006
	Crimp range*		0,75-2,5mm ²	
9 Pole (8+1)		KRS9G20-553 1202310007	KRS9G20-423 1202310008	KRS9G20-003 1202310009
	Crimp range*		0,34-1,0mm ² /0,75-2,5mm ²	
12 Pole		KRSCG20-553 1202310010	KRSCG20-023 1202310011	KRSCG20-003 1202310012
	Crimp range*		0,34-1,0mm ²	
16 Pole		KRSHG20-553 1202310013	KRSHG20-023 1202310014	KRSHG20-003 1202310015
	Crimp range*		0,34-1,0mm ²	
17 Pole		KRSJG20-553 1202310016	KRSJG20-023 1202310017	KRSJG20-003 1202310018
	Crimp range*		0,34-1,0mm ²	
19 Pole (16+3)		KRSLG20-553 1202310019	KRSLG20-223 1202310020	KRSLG20-003 1202310021
	Crimp range*		0,34-1,0mm ² /0,56-1,0mm ²	

*Crimp range only applies to "Crimp Contacts" version



Notes:
Tolerances (unless specified): DIN ISO 2768 m

DESCRIPTION EC NO: WEU2009-0135 DRWN: BBRAUCH 2008/11/14 CH'KD: ---- APPR: JKOLB 2009/03/02	QUALITY SYMBOLS ▽ = 0 ▽C = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE		SCALE	DESIGN UNITS	 FIRST ANGLE PROJECTION	
					MM		---	METRIC		
			mm	INCH	DRAWN BY		DATE	M23 FRONT PM RECEPT. FEM FLANGE-MOUNT 4 X DIA 3.2MM		
		4 PLACES	±----	±----	BB		2008/11/14			
		3 PLACES	±----	±----	CHECKED BY		DATE			
		2 PLACES	±0.05	±----	JKO		2008/12/09			
		1 PLACE	±0.1	±----	APPROVED BY		DATE	 MOLEX INCORPORATED		
		ANGULAR ± --- °			----		----			
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO.		DOCUMENT NO.			SHEET NO.
					see table		SD-120231-001	1 OF 1		
1	REV			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					