








WIRING CONFIGURATION



GASKET AND SCREW TYPES



SYMBOLS ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		molex				
	DIMENSION UNITS mm	SCALE 1:1					
	GENERAL TOLERANCES (UNLESS SPECIFIED)		CURRENT REV DESC:				
	ANGULAR TOL ± °		EC NO: 758064 DRWN: APAWLAK01 2023/07/28 CHK'D: RSILLER 2023/07/28 APPR: RSILLER 2023/07/28				
	4 PLACES ± 3 PLACES ± 2 PLACES ± 1 PLACE ± 0 PLACES ±		INITIAL REVISION: DRWN: JMARSZALEK 2012/10/30 APPR: MIWASIECZKO 2012/11/09				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING A3-SIZE	SERIES 121050	MATERIAL NUMBER SEE SHEET 3	CUSTOMER GENERAL MARKET	SHEET NUMBER 1 OF 3

ENGINEERING PART No. KEY MATRIX

E 4 9 2 X X X X X X X X X X X

E - Packing without bag
W - Single Packing
Q - Quick Packing

Number of wires:
1- 2 Wires
2- 3 Wires
3- 4 Wires
5- SMC COMPATIBLE 2 WIRES
6- SMC COMPATIBLE 3 WIRES
7- SMC COMPATIBLE 4 WIRES

Cable type:
See Table

Head Colour:
G - Grey
N - Black
T - Transparent
A - CSA-UL Black
B - CSA-UL Grey

Cable Length in[cm]
050 = 50cm
300 = 300cm
10K = 1000cm

Earth PIN location (see insert orientation table):
1 = Double Earth on 6H & 12H
2 = Earth on 12H
6 = Earth on 6H

INTERNAL CIRCUIT
WIRING CONFIGURATION

VOLTAGE AND LED COLOUR :

1 - 12V	A - 12V	G - 12V
2 - 24V	B - 24V	H - 24V
3 - 48V	C - 48V	K - 48V
4 - 115V	D - 115V	L - 115V
5 - 230V	E - 230V	M - 230V

RED LED GREEN LED YELLOW LED

Type of Gasket and Screw (see sheet 1) :
1 = NBR Profile Gasket + Fixing Screw M2.5x22.5mm
2 = NBR Flat Gasket + Fixing Screw M2.5x22.5mm
3 = Silicone Profile Gasket + Fixing Screw M2.5x22.5mm
4 = Silicone Flat Gasket + Fixing Screw M2.5x22.5mm
T = NBR Profile Gasket + Fixing Screw with Washer M2.5x23mm

CABLE TYPE TABLE

MOLEX PN	NO. OF WIRES CODE (SEE PN MATRIX)	CABLE TYPE	NO. OF WIRES	CROSS SECTION	CABLE O.D.	CABLE JACKET	WIRES COLOR
1210180128	2	A2	3	AWG 20	Ø5.6±0.2 mm	PVC BLACK	BN, BU, GN/YE
1210180284	2	I2	3	0.5mm²	Ø5.5±0.3 mm	PVC GREY	BN, BU, GN/YE
1202092753	2	N2	3	0.5mm²	Ø5.5±0.2 mm	PVC BLACK	BN, BU, GN/YE
1202092439	2	P2	3	0.5mm²	Ø5.5±0.3 mm	PUR BLACK	BN, BU, GN/YE
1210180126	2	B2	3	AWG 20	Ø5.6±0.2 mm	PUR BLACK	BN, BU, GN/YE
1210180122	2	D2	3	0.5mm²	Ø5.5±0.2 mm	PVC GREY	BN, BU, GN/YE
1552200108	2	W2	3	AWG 21	Ø5.6mm	PVC GREY	BN, BU, GN/YE

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
	DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex			
	mm		1:1								
	GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 758064 DRWN: APAWLAK01 2023/07/28 CHK'D: RSILLER 2023/07/28 APPR: RSILLER 2023/07/28			E492XXXXXXXXXX FORM C EN 175301-803					
	ANGULAR TOL ± °										
	4 PLACES ±										
	3 PLACES ±		PRODUCT CUSTOMER DRAWING								
	2 PLACES ±										
	1 PLACE ±										
	0 PLACES ±		DOCUMENT NUMBER			DOC TYPE	DOC PART	REVISION			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
				A3-SIZE	121050	SEE SHEET 3		GENERAL MARKET		2 OF 3	

