






114032K06M020

LENGTH
M001 = .1 METERS
M010 = 1.0 METERS
M100 = 10 METERS

PART NUMBER LEGEND

CABLE LENGTH TOLERANCES	
<.3M [1FT]:	+19mm-0 [+ .75in-0]
.3 - .9M [1 - 3FT]:	+44.5mm-0 [+1.75in-0]
.9 - 1.8M [3 - 6FT]:	+55.6mm-0 [+2.19in-0]
1.8 - 3.7M [6 - 12FT]:	+88.9mm-0 [+3.50in-0]
3.7 - 7.3M [12 - 24FT]:	+165.1mm-0 [+6.50in-0]
7.3-14.6M [24 - 48FT]:	+317.5mm-0 [+12.50in-0]
14.6 - 30.5M [48-100FT]:	+622.3mm-0 [+24.50in-0]
OVER 30M [100FT]	+2% OF FINISHED LENGTH

10	WRAP LABEL	VINYL	BLACK ON YELLOW
9	OVERMOLD	TPE	YELLOW
8	COUPLING NUT, MALE	ZINC DIE CAST	E-COAT BLACK
7	CONTACT PIN	COPPER ALLOY	GOLD
6	MALE INSERT (CENELEC)	TPE	YELLOW
5	COUPLING NUT, FEMALE	ZINC DIE CAST	E-COAT BLACK
4	FRICTION RING	NYLON	WHITE
3	CONTACT SOCKET	COPPER ALLOY	GOLD
2	FEMALE INSERT (CENELEC)	TPE	YELLOW
1	CABLE 16-4 TC/ER	TPE JACKET	YELLOW
ITEM	DESCRIPTION	MATERIAL	FINISH

- NOTES:
1. MATERIAL: AS NOTED
 2. FINISH: AS NOTED
 3. ELECTRICAL:
VOLTAGE: 600V
CURRENT: 8A
 4. TEMP RATING: -20° TO +90°C
 5. PROTECTION: IP67 (WHEN MATED)
 6. ALL DIMS ARE FOR REFERENCE UNLESS TOLERANCED OR NOTED OTHERWISE

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
DIVISIONAL SYMBOLS	DIMENSION UNITS		SCALE		CURRENT REV DESC: INITIAL CREATION			molex									
	INCH/MM		1:1														
	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 752666 DRWN: HENRYB1 2023/06/12 CHK'D: RSTONE 2023/06/27 APPR: BWOODMAN 2023/06/27			MINI-CHANGE CORDSET CENELEC 4 POLE 90D MALE TO STRAIGHT FEMALE 16/4 TPE									
	MM		INCH														
	4 PLACES ± ±																
	3 PLACES ± ±																
	2 PLACES ± ±																
	1 PLACE ± ±		INITIAL REVISION: DRWN: HBIZNEK 2023/06/12 APPR: BWOODMAN --/--/--			PRODUCT CUSTOMER DRAWING											
	0 PLACES ± ±																
	ANGULAR TOL ± °																
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
						B-SIZE		130010		1300109039		PSD		000		A	
										MATERIAL NUMBER		CUSTOMER				SHEET NUMBER	
																1 OF 1	