



12	11	10	9	8	7	6	5	4	3	2	1
LOOSE PIECE		TAPE MOUNTED		SPECIFICATIONS							
MATERIAL NUMBER	ENGINEERING NUMBER	MATERIAL NUMBER	ENGINEERING NUMBER	STUD SIZE	"S" ±.005 [0.13]	"W"	"C" MIN.	"E" MAX.	"L" MAX.	"H"	
191930254	F-366-10	---	---	10	.198 [5.03]	.665±.013 [16.89±0.33]	.520 [13.21]	1.028 [26.11]	1.385 [35.18]	1.172 [29.77]	
191930258	F-366-12	---	---	12	.515 [13.08]						
191930261	F-366-14	191930263	F-366-14T	14	.265 [6.73]						
191930264	F-366-38	191930266	F-366-38T	38	.390 [9.91]						
191930267	F-366-56	191930269	F-366-56T	56	.328 [8.33]						
191930270	F-366-76	---	---	76	.453 [11.51]	.475±.010 [12.06±0.25]	.520 [13.21]	1.028 [26.11]	1.288 [32.72]	1.172 [29.77]	
191930273	F-367-10	191930274	F-367-10T	10	.198 [5.03]						
191930275	F-367-14	191930277	F-367-14T	14	.265 [6.73]						
191930278	F-367-56	---	---	56	.328 [8.33]	.885±.010 [22.48±0.25]	.989 [25.12]	1.497 [38.02]	1.970 [50.04]	---	
191930281	F-369-12	---	---	12	.515 [13.08]						
191930283	F-369-38	---	---	38	.390 [9.91]						
191930285	F-369-58	---	---	58	.656 [16.66]	1.260±.010 [32.00±0.25]	.989 [25.12]	1.497 [38.02]	2.158 [54.81]	---	
191930287	F-370-12	---	---	12	.515 [13.08]						
191930289	F-370-34	---	---	34	.781 [19.84]						
191930291	F-370-38	---	---	38	.390 [9.91]						
191930293	F-370-58	---	---	58	.656 [16.66]						

NOTES:

1. MATERIAL: COPPER
PLATING: ELECTRO-TIN (.0003 MIN).
2. BRAZED SEAM
3. WIRE SIZE: 4 AWG
25 MM²
4. "UL" LISTING #E32244
"CSA" LISTING #18689
5. ALL DIMENSIONS IN INCHES/[MM].
6. PARTS ARE ROHS COMPLIANT.
7. DIMS. SHOWN ARE FOR REFERENCE ONLY.



PARTS ON TAPE

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

INCH/MM

SCALE

NTS

GENERAL TOLERANCES
(UNLESS SPECIFIED)

MM

INCH

4 PLACES

±

±

3 PLACES

±

± 0.005

2 PLACES

±

0.13

± 0.01

1 PLACE

±

0.25

±

0 PLACES

±

±

ANGULAR TOL

±

0.5 °

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

THIRD ANGLE PROJECTION

DRAWING

C-SIZE

SERIES

19193

CURRENT REV DESC: REMOVED OBSOLETE PART
NUMBERS AS PER PCN#515181

EC NO: 793824

DRWN: MADHAM5

CHK'D: GGA

APPR: GGA

2024/05/22

2024/08/14

2024/08/14

INITIAL REVISION:

DRWN: LEM

APPR: JMACNEIL

1970/03/02

2019/08/06

DOCUMENT NUMBER

191930254

DOC TYPE

PSD

DOC PART

000

REVISION

A1

molex

RING TONGUE TERMINAL
VERSAKRIMP

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER

191930254

CUSTOMER

GENERAL MARKET

SHEET NUMBER

1 OF 1