


CIRCUIT SIZE LAYOUT
(NOT TO SCALE)

PART NUMBER		CKT SIZE	DIM "A"	DIM "B"	MATERIAL CODE & COLOR △
46992-0240		02	.21/5.40	--	250BS BLUE (V0)
46992-0440		04	.38/9.60	.165/4.20	
46992-0640		06	.54/13.8	.331/8.40	
46992-0840		08	.71/18.0	.496/12.60	
46992-1040		10	.87/22.2	.661/16.8	
46992-1240		12	1.04/26.4	.827/21.00	
46992-0250		02	.21/5.40	--	250WS NATURAL (V0)
46992-0450		04	.38/9.60	.165/4.20	
46992-0650		06	.54/13.8	.331/8.40	
46992-0850		08	.71/18.0	.496/12.60	
46992-1050		10	.87/22.2	.661/16.8	
46992-1250		12	1.04/26.4	.827/21.00	

PART NUMBER		CKT SIZE	DIM "A"	DIM "B"	MATERIAL CODE & COLOR ⚠
46992-0200		02	.21/5.40	--	225NS NATURAL (V2)
46992-0400		04	.38/9.60	.165/4.20	
46992-0600		06	.54/13.8	.331/8.40	
46992-0800		08	.71/18.0	.496/12.60	
46992-1000		10	.87/22.2	.661/16.8	
46992-1200		12	1.04/26.4	.827/21.00	
46992-1400		14	1.21 / 30.6	.992/25.20	
46992-1600		16	1.37 / 34.8	1.158/29.40	
46992-1800		18	1.54 / 39.0	1.323/33.60	
46992-2000	X	20	1.70 / 43.2	1.488/37.80	
46992-2200	X	22	1.87 / 47.4	1.654/42.00	
46992-2400	X	24	2.03 / 51.6	1.819/46.20	
46992-0210		02	.21/5.40	--	225S BLACK (V2)
46992-0410		04	.38/9.60	.165/4.20	
46992-0610		06	.54/13.8	.331/8.40	
46992-0810		08	.71/18.0	.496/12.60	
46992-1010		10	.87/22.2	.661/16.8	
46992-1210		12	1.04/26.4	.827/21.00	
46992-1410		14	1.21 / 30.6	.992/25.20	
46992-1610		16	1.37 / 34.8	1.158/29.40	
46992-1810		18	1.54 / 39.0	1.323/33.60	
46992-2010	X	20	1.70 / 43.2	1.488/37.80	
46992-2210	X	22	1.87 / 47.4	1.654/42.00	
46992-2410		24	2.03 / 51.6	1.819/46.20	
46992-0220		02	.21/5.40	--	250RS RED (V0)
46992-0420		04	.38/9.60	.165/4.20	
46992-0620		06	.54/13.8	.331/8.40	
46992-0820		08	.71/18.0	.496/12.60	
46992-1020		10	.87/22.2	.661/16.8	
46992-1220		12	1.04/26.4	.827/21.00	
46992-0230		02	.21/5.40	--	250GS GREEN (V0)
46992-0430		04	.38/9.60	.165/4.20	
46992-0630		06	.54/13.8	.331/8.40	
46992-0830		08	.71/18.0	.496/12.60	
46992-1030		10	.87/22.2	.661/16.8	
46992-1230		12	1.04/26.4	.827/21.00	
X = NOT TOOLED					

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex					
mm		NTS												
GENERAL TOLERANCES (UNLESS SPECIFIED)									MINIFIT JR RECEPTACLE HOUSING DUAL ROW, 2-24 CKT					
	MM	INCH												
4 PLACES	±		±	EC NO: 776137 DRWN: JERRYW8 2024/02/01 CHK'D: XQZHANG 2024/02/22 APPR: XQZHANG 2024/02/22					PRODUCT CUSTOMER DRAWING					
3 PLACES	±		± 0.01											
2 PLACES	±	0.25	± 0.015											
1 PLACE	±	0.38	±	INITIAL REVISION: DRWN: NNGUYEN 2013/04/12 APPR: FSMITH 2014/05/16					DOCUMENT NUMBER			DOC TYPE	DOC PART	REVISION
0 PLACES	±		±						SD-46992-0000			PSD	000	A10
ANGULAR TOL ± 3.0 °				THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER			SHEET NUMBER	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						C-SIZE	46992	SEE TABLE		GENERAL MARKET			2 OF 2	

DOCUMENT STATUS	P1	RELEASE DATE	2024/02/22	08:10:02
-----------------	----	--------------	------------	----------