



Insulated Screwdriver, 3/32-Inch Cabinet, 3-Inch Round Shank



Protect yourself when working near an energized source. Clearly marked with the official 1000-volt rating symbol, Klein insulated tools exceed IEC 60900 and ASTM F1505 standards for insulated tools. Two layers of insulation provide protection against electric shock. Perfect for working in control boxes or other terminal block applications where insulated tools are necessary.

Specifications

Application:	For Work Near Energized Sources	Special Features:	Flame Retardant and Impact Resistant Handle
Tip Type:	Cabinet	Magnetic:	No
Tip Size:	3/32" (2.4 mm)	Shank Type:	Round
Shank Length:	3" (7.6 cm)	Material:	Induction Hardened Steel
Insulated:	Yes	Handle Material:	High-Dielectric Plastic
Handle Color:	Black	Overall Length:	6.75" (17.2 cm)
Standard:	IEC 60900 and ASTM F1505	Weight:	1.9 oz (54 g)