



Insulated Long Nose Pliers, Side-Cutting/Stripping



These Klein Tools long nose side-cutting/stripping pliers are made of forged steel for maximum durability. They have a heavier design and extended handles to improve leverage and power. And they have two layer bright orange insulation that is both flame retardant and provide electric protection for up to 1000 V.

Specifications

Type:	Long Nose	Application:	For Work Near Energized Sources
Special Features:	Flame Retardant and Impact Resistant Handle	Overall Length:	8.91" (22.6 cm)
Material:	Induction Hardened Steel	Jaw Length:	2.32" (5.9 cm)
Jaw Width:	1.02" (2.6 cm)	Jaw Thickness:	0.5" (1.3 cm)
Jaw Capacity:	2.36" (6 cm)	Point Diameter:	0.125" (0.32 cm)
Cutting Knives:	Standard	Knife Length:	0.693" (1.8 cm)
Cut Style:	Side-Cutting and Skinning	Joint Type:	Hot-Riveted
Handle Color:	Orange	Handle Finish:	2-Layer Insulation
Handle Length:	4.79" (12.2 cm)	Insulated:	Yes
Standard:	IEC 60900 and ASTM F1505	Weight:	11.2 oz (318 g)