



Lineman's Bolt-Thread Holding Pliers, 9-Inch



The hinge opening on Klein's Lineman's Bolt-Thread Holding Pliers holds and cleans 5/8" (16 mm) pole line and hardware bolts or threaded rods. The plier head is precision-hardened for on-the-job toughness. The exclusive handle tempering helps absorb the "snap" when cutting wire helping reduce fatigue.

Specifications

Type:	Side Cutting Pliers	Application:	Core High Leverage Side Cutting Features Plus: 5/8" (1.59 mm) Pole Line and Hardware Bolts, Threaded Rods
Overall Length:	9.35" (23.7 cm)	Overall Height:	0.75" (1.9 cm)
Overall Width:	2.06" (5.2 cm)	Material:	Induction Hardened Steel
Nose Type:	New England	Jaw Length:	1.91" (4.9 cm)
Jaw Width:	1.25" (3.2 cm)	Jaw Thickness:	0.62" (1.6 cm)
Jaw Capacity:	1.375" (3.5 cm)	Cutting Knives:	1
Knife Length:	0.797" (2 cm)	Cut Style:	Side-Cutting
Screw Shearing:	No	Joint Type:	Hot-Riveted
Handle Color:	Dark Blue	Handle Finish:	Plastic-Dipped
Handle Length:	5.41" (13.7 cm)	Insulated:	No
Tether Capable:	No	Weight:	1.1 lb (0.5 kg)