


10MAX	50MAX	100MAX	250MAX	250OVR	ANGLE	ECCENT
TOLERANCE	±0.5	±0.8	±1.5	±2.5	±3	±5°
						0.3

1


2

3

YAZAKI PART NO	TREAT. & FIN.	MASS
7003-2455		23.6g
7003-2455-02	※R50X※:5um以上 銅接地※:1um以上	23.6g



BLANK FORM



注記
1. 適用電線サイズ: AV(EB)40

NOTE
1. APPLICABEL WIRE SIZE: AV(EB)40

CUSTOMER		CUSTOMER PART NO.		CUSTOMER DWG NO.		MATERIAL SPEC.		TREAT. & FIN.		ISSUE MARK	
06.03.28 RENEW & ADDED PART NO.		C06-0069		M. I		C2801(t=2.3)		SEE TABLE			
93.05.14 NEW		C93-0430		M. I		NAME		TERMINAL			
REVISION RECORD		NO.		CHKD		TRIAL PART NO.					
DATE				VENDOR		VENDOR NO.					
GENERAL TOLERANCE											
10MAX		50MAX		100MAX		250MAX		250OVR		ANGLE ECCENT	
A ±0.15		±0.2		±0.3		±0.5		±0.75		±30° 0.1	
B ±0.2		±0.3		±0.55		±0.95		±1.4		±30° 0.1	
C ±0.3		±0.5		±0.8		±1.4		±2		±30° 0.15	
SPECIFIED		SEE TABLE		MASS		9					

1

2

3