




RUBBER PART GENERAL TOLERANCE				
PART DIM.	1	2	③	
0 TO 3	± 0.2	± 0.3	± 0.4	
3 TO 6	± 0.2	± 0.4	± 0.5	
6 TO 10	± 0.3	± 0.5	± 0.6	
10 TO 18	± 0.3	± 0.6	± 0.8	
18 TO 30	± 0.4	± 0.8	± 1.0	
30 TO 50	± 0.5	± 1.0	± 1.5	
50 TO 80	± 0.6	± 1.2	± 2.0	
80 TO 120	± 0.7	± 1.4	± 2.5	
120 TO 180	± 0.8	± 1.6	± 3.0	
180 TO 250	± 1.0	± 2.0	± 4.0	
250 TO 315	± 1.2	± 2.5	± 5.0	
315 TO 400	± 1.5	± 3.0	± 6.0	
400 TO 500	± 1.8	± 3.5	± 7.0	
500 OVER	± 0.4 %	± 0.8 %	± 1.5 %	

注 記



1. 亀裂、気泡及び機能上有害なバリの無き事。

NOTES

1. MUST BE FREE OF FLASH,
BUBBLE AND BURR THAT
AFFECT FUNCTION.



SEC. A-A



LET	DATE	REVISION RECORD	NO.	CHKD
	11. 10. 05	NEW	C11-1086	H. N

GENERAL TOLERANCE									
	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT		
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30°	0.1		
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30°	0.1		
C	±0.3	±0.5	±0.8	±1.4	±2	±30°	0.15		
SPECIFIED							MASS	15 g	

CUSTOMER		MATL. EPDM(BLACK)		TREAT. & FIN.	
CUSTOMER PART NO.		CUSTOMER DWG NO.		NAME GROMMET	
OFFICE		TRIAL PART NO.			
VENDOR					
VENDOR NO.					
DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE
R	NEW	11. 10. 05	mm	1/1	3
APPROVED	CHECKED	CHECKED	DESIGN	DRAWN	
K. SUZUKI	T. TEZUNA	K. TSUCHIYA	KATSUYA -SUZUKI	H. NOGUCHI	
		11. 10. 05	92. 06. 04	11. 10. 05	
		PART NO. 7035-6343			
		DWG NO. 7035-6343:R			
		YAZAKI CORPORATION			

ISSUE MARK