

C

B



A

2





3

4

5



(1/1)



SECTION A-A

- NOTES:
1. PARTS MUST BE PURCHASED FROM YAZAKI.
 2. PARTS MUST BE FREE OF FLASH AND IMPERFECTIONS THAT AFFECT FUNCTION.
 3. TO BE USED WITH: 7287-0973-30
 4. PART TO COMPLY WITH YPES-31-038 REQUIREMENTS.
 5. FOR USE WITH 6mm CONDUIT.
 6. THIS DRAWING IS TO BE USED FOR INTERNAL YAZAKI PSW SUBMISSION.

-	05-29-2013	NEW	C13-A328	MMR
LET	DATE	REVISION RECORD	NO.	CHKD

GENERAL TOLERANCE							
	10 MAX	50 MAX	100 MAX	250 MAX	250 OVR	ANGLE	ECCENT
A	± 0.15	± 0.2	± 0.3	± 0.5	± 0.75	± 30'	0.1
B	± 0.2	± 0.3	± 0.55	± 0.95	± 1.4	± 30'	0.1
C	± 0.3	± 0.5	± 0.8	± 1.4	± 2	± 30'	0.15
SPECIFIED					WEIGHT		
					g		

CUSTOMER		CUSTOMER PART NO.		CUSTOMER DWG NO.	
OFFICE		YNA		STD LIB NO.	
VENDOR					
VENDOR NO.					
DWG TYPE	R	DWG SOURCE	7047-7224-30:R	DWG DATE	05-29-2013
APPROVED		CHECKED		DESIGN	DEREK HARRIS
					09.13.06

MATL. SPEC.	PP (BLACK)	TREAT & FIN.
NAME	2P DELPHI GT 1.5MM SEALED FEMALE ----- CONVOLUTE CLIP	
PART NO.	7047-7224-30	
DWG NO.	7047-7224-30:R	
YAZAKI CORPORATION		

ISSUE MARK

C

B

A

2

3

4

5