

2		3					
A	PART NO.	W ₁	W ₂	H ₁	H ₂	APPLICABLE WIRE SIZE	TREAT. & FIN.
	7116-2873	2.9	6.1	(3.0)	(5.3)	AVS 0.5~ AV 1.25	_____
	7116-2873-02						TIN PLATING
A	7116-2874	4.1	8.0	(4.1)	(6.9)	AVS 2~ AV 3	_____
	7116-2874-02						TIN PLATING

注記




1) かん合雄端子品番 : 7114-2873 ETC.

2) 適用コゝ△栓品番 : 7157-3570 ETC.

NOTES

1) MATING MALE TERMINAL NO. : 7114-2873 ETC.

2) APPLICABLE SEAL RUBBER NO. : 7157-3570 ETC.



SEC. A-A

SEC. B-B

															ISSUE MARK	
△	10. 12. 15	ADDED TREATMENT, ETC.			C10-2737	K. U				MATL. △	BRASS (t=0. 32)			TREAT. △	SEE TABLE	
△	94. 03. 08	CORRECTION OF A CLERICAL ERROR			C94-L405	H. K	CUSTOMER									
					CUSTOMER PART NO.		CUSTOMER DWG. NO.									
△	93. 09. 15	ADDED PART NO.			C93-P145	H. F				NAME						
	89. 02. 07	NEW			C89-L260	T. M	OFFICE			X TYPE TERMINAL F						
LET	DATE	REVISION RECORD			NO.	CHKD	VENDOR			-----						
GENERAL TOLERANCE																
						VENDOR NO.										
	10MAX	50MAX	100MAX	250MAX	250OVR	ANGLE	ECCENT	DWG. TYPE		DWG. SOURCE	DWG. DATE	UNIT	SCL	ANGLE	PART NO.	
A	±0. 15	±0. 2	±0. 3	±0. 5	±0. 75	±30'	0. 1	R	NEW	89. 02. 09	mm	5:1	3		7 1 1 6 - 2 8 7 3	ETC.
B	±0. 2	±0. 3	±0. 55	±0. 95	±1. 4	±30'	0. 1	APPROVED		CHECKED	CHECKED	DESIGN	DRAWN		DWG. NO.	7 1 1 6 - 2 8 7 3 : R
①	±0. 3	±0. 5	±0. 8	±1. 4	±2	±30'	0. 15	M. KASHIYAMA		K. URANO	ISHIZUKA		J. GAMBOA			
SPECIFIED						MASS		10. 12. 15		10. 12. 15	-----		82. 05. 01	10. 12. 15	YAZAKI CORPORATION	



ω