




NOTE
1) APPLICABLE TERMINAL NO.: 7125-1481,
7125-1482.
2) 適用端子番: 7125-1481,
7125-1482.

SEC. A-A

GENERAL TOLERANCE									
10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT			
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30°	0.1		
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30°	0.15		
C	±0.3	±0.5	±0.8	±1.4	±2	±30°	0.15		
SPECIFIED							WEIGHT		

91.02.14	CHANGED FORM	C91-6307	Y.T
89.02.04	NEW	C89-L224	M.Y
LET DATE	REVISION RECORD	NO.	CHKD

CUSTOMER PART NO.	CUSTOMER DWG NO.	MATL. SPEC.	P. B. T (NATURAL)	TREAT. & FIN.
OFFICE	STD LIB NO.	NAME	SMC 10P HOUSING	
VENDOR		PART NO.	7125-2701	
		DWG NO.	7125-2701-R	
		TRIAL PART NO.		
			YAZAKI CORPORATION	

91.02.26	91.02.26	87.09.30	91.02.26
3	3	4	4