





SEC. A-A



CONNECTOR MATING SURFACE (2/1)

NOTES:

1. MATING HOLE: $\phi 6.5$, $t=0.56-5.10$
2. MATING PARTS (FOR REFERENCE ONLY):
050, 09011, 187 & 312 CONNECTOR SERIES
WITH MATING SURFACE AS SHOWN ABOVE.
REFERENCE PART NUMBER 7182-4421
3. MATERIAL: NYLON 6/6 (BLACK)
4. MUST BE FREE OF FLASH AND IMPERFECTIONS THAT AFFECT FUNCTION.
PROPER FUNCTIONALITY TO BE DETERMINED BY THE APPROPRIATE
YAZAKI ENGINEERING AFFILIATE.

GENERAL TOLERANCE			
	10MAX	50MAX	100MAX
A	±0.15	±0.2	±0.3
B	±0.2	±0.3	±0.5
C	±0.3	±0.5	±0.8
ANG	±30°	±30°	±30°
ECC	0.1	0.1	0.1
CON	0.1	0.1	0.1
MASS	±0.15	±0.4	±1.4

LET	DATE	REVISION	RECORD	NO.	CHKD
	04/25/08	NEW		C08-A454	EB
					CHKD

CUSTOMER	CHRYSLER	CUSTOMER PART NO.	CUSTOMER Dwg NO.	MATL. SPEC.	SEE NOTE #3	TREAT. & FIN.	ISSUE MARK
OFFICE	YNA CANTON						
VENDOR							
NAME	CONNECTOR CLIP (9MM)						
UNIT	(T-300, N-BODY, ZJ)						
DATE	04/25/08	DESIGN	2/1	3			
APPROVED		CHECKED					
PRZEMODEK							
DATE	05/03/04	04/27/08					
PART NO.	7147-8717-30						
DWG NO.	7147-8717-30:R						
YAZAKI CORPORATION							