

| RUBBER PART GENERAL TOLERANCE |      |         |         |         |   |
|-------------------------------|------|---------|---------|---------|---|
| PART DIM.                     | 1    |         | 2       |         | ③ |
|                               | 0 TO | ± 0.2   | ± 0.3   | ± 0.4   |   |
| 3 TO                          | 6    | ± 0.2   | ± 0.4   | ± 0.5   |   |
| 6 TO                          | 10   | ± 0.3   | ± 0.5   | ± 0.6   |   |
| 10 TO                         | 18   | ± 0.3   | ± 0.6   | ± 0.8   |   |
| 18 TO                         | 30   | ± 0.4   | ± 0.8   | ± 1.0   |   |
| 30 TO                         | 50   | ± 0.5   | ± 1.0   | ± 1.5   |   |
| 50 TO                         | 80   | ± 0.6   | ± 1.2   | ± 2.0   |   |
| 80 TO                         | 120  | ± 0.7   | ± 1.4   | ± 2.5   |   |
| 120 TO                        | 180  | ± 0.8   | ± 1.6   | ± 3.0   |   |
| 180 TO                        | 250  | ± 1.0   | ± 2.0   | ± 4.0   |   |
| 250 TO                        | 315  | ± 1.2   | ± 2.5   | ± 5.0   |   |
| 315 TO                        | 400  | ± 1.5   | ± 3.0   | ± 6.0   |   |
| 400 TO                        | 500  | ± 1.8   | ± 3.5   | ± 7.0   |   |
| 500 OVER                      |      | ± 0.4 % | ± 0.8 % | ± 1.5 % | % |

附  
表

1. 適用コネクタ品番: 7222-6524-40 ETC.




2. ゴム材料：含油シリコンゴム（黒青）

NOTES

1. APPLICABLE CONNECTOR NO. : 7222-6524-40 ETC.

2. RUBBER MATERIAL : SELF LUBRICATION SILICONE RUBBER

: (LIGHT BLUE)



|           |  |          |  |                 |  |                   |  |        |  |                  |  |                         |  |               |  |  |  |
|-----------|--|----------|--|-----------------|--|-------------------|--|--------|--|------------------|--|-------------------------|--|---------------|--|--|--|
|           |  |          |  |                 |  |                   |  |        |  | MTRL. SPEC.      |  | SEE NOTES               |  | TREAT. & FIN. |  |  |  |
|           |  |          |  |                 |  |                   |  |        |  | NAME             |  | SEALED PLUG FOR RV-TYPE |  |               |  |  |  |
|           |  |          |  |                 |  |                   |  |        |  | PART NO.         |  | 7157-3990-90            |  |               |  |  |  |
|           |  |          |  |                 |  |                   |  |        |  | CH. CODE         |  |                         |  |               |  |  |  |
|           |  |          |  |                 |  |                   |  |        |  | DWG NO.          |  | 7157-3990-90:R          |  |               |  |  |  |
|           |  |          |  |                 |  |                   |  |        |  |                  |  | YAZAKI CORPORATION      |  |               |  |  |  |
|           |  | CUSTOMER |  |                 |  | CUSTOMER PART NO. |  |        |  | CUSTOMER DWG NO. |  |                         |  |               |  |  |  |
|           |  |          |  |                 |  |                   |  |        |  |                  |  |                         |  |               |  |  |  |
| 94.03.31  |  | NEW      |  | C94-L452        |  | S. K              |  |        |  | OFFICE           |  |                         |  |               |  |  |  |
|           |  |          |  |                 |  |                   |  |        |  | TRIAL PART NO.   |  |                         |  |               |  |  |  |
| LET       |  | DATE     |  | REVISION RECORD |  | NO.               |  | CHKD   |  | VENDOR           |  |                         |  |               |  |  |  |
|           |  |          |  |                 |  |                   |  |        |  | VENDOR NO.       |  |                         |  |               |  |  |  |
| 10MAX     |  | 50MAX    |  | 100MAX          |  | 250MAX            |  | 250QVR |  | DWG TYPE         |  | DWG SOURCE              |  | DWG DATE      |  |  |  |
| A         |  | ±0.15    |  | ±0.2            |  | ±0.3              |  | ±0.5   |  | R                |  | NEW                     |  | 94.03.30      |  |  |  |
| B         |  | ±0.2     |  | ±0.3            |  | ±0.55             |  | ±1.4   |  | APPROVED         |  | CHECKED                 |  | DESIGN        |  |  |  |
| C         |  | ±0.3     |  | ±0.5            |  | ±0.8              |  | ±2     |  | 11木              |  |                         |  | K. ABE        |  |  |  |
| SPECIFIED |  |          |  |                 |  |                   |  | MASS   |  | 94.3.31          |  | 94.3.31                 |  | 91.10.08      |  |  |  |
|           |  |          |  |                 |  |                   |  | g      |  |                  |  |                         |  | 94.03.31      |  |  |  |