

RUBBER PART GENERAL TOLERANCE				SEAL RUBBER PART NO.	COLOR	APPLICABLE WIRE SIZE
PART DIM.	1	2	③			
0 TO 3	± 0.2	± 0.3	± 0.4	7157-3570	BLACK	(AVS) AV 0.5 ~ AV 1.25
3 TO 6	± 0.2	± 0.4	± 0.5			(AVS)
6 TO 10	± 0.3	± 0.5	± 0.6	7157-3571-80	BROWN	AV 2 ~ AV 3
10 TO 18	± 0.3	± 0.6	± 0.8			
18 TO 30	± 0.4	± 0.8	± 1.0			
30 TO 50	± 0.5	± 1.0	± 1.5			
50 TO 80	± 0.6	± 1.2	± 2.0			
80 TO 120	± 0.7	± 1.4	± 2.5			
120 TO 180	± 0.8	± 1.6	± 3.0			
180 TO 250	± 1.0	± 2.0	± 4.0			
250 TO 315	± 1.2	± 2.5	± 5.0			
315 TO 400	± 1.5	± 3.0	± 6.0			
400 TO 500	± 1.8	± 3.5	± 7.0			
500 OVER	± 0.4 %	± 0.8 %	± 1.5 %			

△ 注

1) 通明ターミナル品番: 7114-2873 ETC.

: 7116-2873 ETC.



2) 通明ハウジング品番: 7122-6224-40, 7223-6224-40 ETC.

△ NOTES

1) APPLICABLE TERMINAL PART NO: 7114-2873 ETC.

: 7116-2873 ETC.

2) APPLICABLE HOUSING NO. : 7122-6224-40, 7223-6224-40 ETC.



MAT'L. SPEC. △ SILICONE RUBBER		TREAT. & FIN.	
NAME X-TYPE CONNECTOR		SEAL RUBBER	
PART NO.	7157-3570 ETC.	CH. CODE	
DWG NO.	7157-3570:R	SET	SET DRW NO.
YAZAKI CORPORATION			
3			

CUSTOMER		CUSTOMER DWG NO.	
CUSTOMER PART NO.		TRIAL PART NO.	
OFFICE			
VENDOR			
VENDOR NO.			
DWG TYPE	DWG SOURCE	DWG DATE	UNIT
R	RENEW	90/07/02	mm
APPROVED	CHECKED	DESIGN	DRAWN
伊山	地木	ISHIZUKA	D. GABRIEL
105.02.14	05.02.14	83/01/06	05/02/09
SPECIFIED		9	

05/02/09	CHANGED TOLERANCE ETC.	C05-Z201	K. I
90/07/20	RENEW	C90-6847	A. H
LET DATE	REVISION RECORD	NO.	CHKD
GENERAL TOLERANCE			
10MAX	50MAX	100MAX	250MAX
±0.15	±0.2	±0.3	±0.5
±0.2	±0.3	±0.55	±1.4
±0.3	±0.5	±0.8	±1.4
±0.15			
MASS			