


1


2

3

Ø 5.80



Ø 4.80



RUBBER PART GENERAL TOLERANCE			
PART DIM.	1	2	3
0 TO 3	± 0.2	± 0.3	± 0.4
3 TO 6	± 0.2	± 0.4	± 0.5
6 TO 10	± 0.3	± 0.5	± 0.6
10 TO 18	± 0.3	± 0.6	± 0.8
18 TO 30	± 0.4	± 0.8	± 1.0
30 TO 50	± 0.5	± 1.0	± 1.5
50 TO 80	± 0.6	± 1.2	± 2.0
80 TO 120	± 0.7	± 1.4	± 2.5
120 TO 180	± 0.8	± 1.6	± 3.0
180 TO 250	± 1.0	± 2.0	± 4.0
250 TO 315	± 1.2	± 2.5	± 5.0
315 TO 400	± 1.5	± 3.0	± 6.0
400 TO 500	± 1.8	± 3.5	± 7.0
500 OVER	± 0.4 %	± 0.8 %	± 1.5 %

注意
1. 金型リコネ
色: ベルグレン

NOTE
1. SELF-LUBRICATING SILICONE RUBBER
COLOR: RED-IRON

ISSUE MARK

MATL. SEE NOTE
SPEC. & FIN.

NAME 090 SEALED CONNECTOR
PLUGGING RUBBER STOPPER

PART NO. 7157-8761

DNG NO. 7157-8761:R

YAZAKI CORPORATION

91.10.04 NEW
LET DATE REVISION RECORD

C91-L764
NO. CHKD

GENERAL TOLERANCE

	10MAX	50MAX	100MAX	250MAX	500MAX	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30°	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30°	0.1
C	±0.3	±0.5	±0.8	±1.4	±2	±30°	0.15

SPECIFIED

MASS

9

CUSTOMER
CUSTOMER PART NO.

CUSTOMER DNG NO.

OFFICE

VENDOR

VENDOR NO.

TRIAL PART NO.

DNG TYPE

DNG SOURCE

DNG DATE

UNIT

SCL

ANGLE

PART NO.

7157-8761

DNG NO.

7157-8761:R

YAZAKI CORPORATION

ISSUE MARK

YAZAKI CORPORATION