



PART	RUBBER PART GENERAL TOLERANCE			③
	DIM.	1	2	
0 TO	3	± 0.2	± 0.3	± 0.4
3 TO	6	± 0.2	± 0.4	± 0.5
6 TO	10	± 0.3	± 0.5	± 0.6
10 TO	18	± 0.3	± 0.6	± 0.8
18 TO	30	± 0.4	± 0.8	± 1.0
30 TO	50	± 0.5	± 1.0	± 1.5
50 TO	80	± 0.6	± 1.2	± 2.0
80 TO	120	± 0.7	± 1.4	± 2.5
120 TO	180	± 0.8	± 1.6	± 3.0
180 TO	250	± 1.0	± 2.0	± 4.0
250 TO	315	± 1.2	± 2.5	± 5.0
315 TO	400	± 1.5	± 3.0	± 6.0
400 TO	500	± 1.8	± 3.5	± 7.0
500 OVER		± 0.4 %	± 0.8 %	± 1.5 %

2. 强

- 1) 取扱説明書No. : YPES-15-221
- 2) 本製品の性能は、JASO D616:2011版 (分類2) を満足すること。

2. NOTES

- 1) HANDLING MANUAL NO. : YPES-15-221
- 2) THE PERFORMANCE OF THIS PRODUCT MUST BE IN ACCORDANCE WITH JASO D616:2011th EDITION (CLASSIFICATION 2).

[illegible]