

1	2	3	4	5	6	7
YAZAKI PART NO.	YAZAKI PART NAME	COLOR	MATING PART NO.	NO.	COMPOSITION PARTS	QTY.
7182-4940-90	DOUBLE SIDED J/C 24P (12PX2)	BLUE	7283-5092-90	①	7114-9017-02 090 □ SHORT TERMINAL 12P	2
7182-4943-40	DOUBLE SIDED J/C 24P (12P+6PX2)	LIGHT GRAY	7283-5092-40	① ②	7114-9017-02 090 □ SHORT TERMINAL 12P 7114-9015-02 090 □ SHORT TERMINAL 6P	1 2
7182-4942-30	DOUBLE SIDED J/C 24P (4PX3+6PX2)	BLACK	7283-5092-30	② ③	7114-9015-02 090 □ SHORT TERMINAL 6P 7114-9016-02 090 □ SHORT TERMINAL 4P	2 3
7182-4941	DOUBLE SIDED J/C 24P (4PX6)	NATURAL	7283-5092	③	7114-9016-02 090 □ SHORT TERMINAL 4P	6

C2680-H t=0.64 TIN PLATE
C2680-H t=0.64 TIN PLATE
C2680-H t=0.64 TIN PLATE
C2680-H t=0.64 TIN PLATE
C2680-H t=0.64 TIN PLATE



7182-4940-90



7182-4942-30



7182-4943-40



7182-4941

7182-4940-90	7182-4942-30	7182-4943-40	7182-4941
--------------	--------------	--------------	-----------

CUSTOMER	CUSTOMER PART NO.	CUSTOMER DWG NO.	MATL. SPEC.	P. P	TREAT. & FIN.	ISSUE MARK
OFFICE						
WORKS						
TRIAL PART NO.	7283-5092-90					
VER. NO.						
DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	PART NO.
R	NEW	95.03.01	mm	2/1	3	CH. CODE
APPROVED	CHECKED	DESIGN	DRAWN			DWG NO.
宮本	寺田	宮本	SEKI	J.VERS02A		
MASS	12.8g					
SPECIFIED						