


7183-6097



△ 7183-6097-90

△ 7183-6097-40




7183-6152 (リブ違い品)

△ 7183-6152-60



24.70



22.35

(13.55)

3.50

10.50

17.50

PART NO. AND CH. CODE	COLOR
7183-6097	NATURAL
7183-6152	NATURAL
△ 7183-6152-60	GREEN
△ 7183-6097-90	BLUE
△ 7183-6097-40	LIGHT GRAY

注 記

- △ 1) かん合相手品番 : 7183-6152 : A (直結専用)
: 7183-6097 : A (直結専用)
: 7182-6097
- △ 2) 適用端子品番 : 7116-4780-02 (CAVS 0.3~0.5)
: 7116-4781-02 (CAVS 0.85~1.25)

NOTES

- △ 1) MATING PART NO. : 7183-6152 : A (DIRECT)
: 7183-6097 : A (DIRECT)
: 7182-6097
- △ 2) APPLICABLE TERMINAL NO. : 7116-4780-02 (CAVS 0.3~0.5)
: 7116-4781-02 (CAVS 0.85~1.25)



GENERAL TOLERANCE													
	10MAX	50MAX	100MAX	250MAX	250OVR	R5 MAX	R10 MAX	R20 MAX	R20 OVR	ANGLE	ECCENT		
A	±0.15	±0.2	±0.3	±0.5	±0.75	±0.2	±0.3	±0.5	±2.5	±3°	0.1		
B	±0.2	±0.3	±0.55	±0.95	±1.4					±3°	0.1		
C	±0.3	±0.5	±0.8	±1.4	±2					±3°	0.15		
CUSTOMER						MATL. SPEC. PBT				TREAT. & FIN.			
CUSTOMER PART NO.				CUSTOMER DWG NO.				NAME Δ 060 6P HOUSING FEMALE					
OFFICE				TRIAL PART NO.									
VENDOR													
VENDOR NO.													
DWG TYPE	DWG SOURCE		DWG DATE		UNIT	SCL	ANGLE	PART NO. 7183-6097 ETC.					
R	NEW		01.10.11		mm	2:1	3	CH. CODE					
APPROVED	CHECKED	CHECKED		DESIGN		DRAWN		DWG NO. 7183-6097:R				SET DWG NO.	
S. MIZUSE	_____	R. DE GUZMAN		S. KAYAMA		M. ALAGAR		YAZAKI CORPORATION					
10.11.15	_____	10.11.15		00.10.26		10.11.15							

4	10. 11. 15	CHANGED PART NAME	C10-ZB09	M. A			
3	08. 11. 13	ADDED COLOR PART NO.	C08-Z826	M. M			
2	07. 04. 04	CHANGED NOTES	C07-Z166	M. M			
1	03. 09. 19	CHANGED TOLERANCE & ADDED COLOR PART NO.	C03-X581	M. M			
	01. 10. 11	NEW	C01-Y079	K. Y			
LET	DATE	REVISION RECORD	NO.	CHKD			
GENERAL TOLERANCE							
	10MAX	50MAX	100MAX	250MAX	250OVR	ANGLE	ECCEN
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1
C	±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15
SPECIFIED						MASS	