

| GENERAL TOLERANCE |        |        |         |         |         |        |         |         |         |
|-------------------|--------|--------|---------|---------|---------|--------|---------|---------|---------|
|                   | 10 MAX | 50 MAX | 100 MAX | 250 MAX | 250 OVR | R5 MAX | R10 MAX | R20 MAX | R20 OVR |
| A                 | ±0.15  | ±0.2   | ±0.3    | ±0.5    | ±0.75   |        |         |         |         |
| B                 | ±0.2   | ±0.3   | ±0.55   | ±0.95   | ±1.4    | ±0.2   | ±0.3    | ±0.5    | ±2.5    |
| (C)               | ±0.3   | ±0.5   | ±0.8    | ±1.4    | ±2      |        |         |         |         |
|                   |        |        |         |         |         |        |         |         |         |
|                   | ANGLE  | ECCENT |         | ECCENT  |         | ECCENT |         | ECCENT  |         |
| A                 | ±3°    | 0.1    |         | 0.1     |         | 0.1    |         | 0.1     |         |
| B                 | ±3°    | 0.1    |         | 0.1     |         | 0.1    |         | 0.1     |         |
| (C)               | ±3°    | 0.15   |         | 0.15    |         | 0.15   |         | 0.15    |         |




| PART NO.<br>AND CH. CODE                      | COLOR      |
|-----------------------------------------------|------------|
| 7183-2510- <u>A</u><br>(7B83-2510- <u>A</u> ) | NATURAL    |
| 7183-2510-30- <u>A</u>                        | BLACK      |
| 7183-2510-40- <u>A</u>                        | LIGHT GRAY |
| 7183-2510-50- <u>A</u>                        | ORANGE     |
| 7183-2510-60- <u>A</u>                        | GREEN      |
| 7183-2510-80- <u>A</u>                        | BROWN      |
| 7183-2510-90- <u>A</u>                        | BLUE       |

注記

1. 材質 : PBT
- 色 : 色番表参照
2. かん合相手品番 : 7282-1080 ETC., 7182-2410
3. 取扱説明書NO. YPES-15-408
4. ( )内品番は、エアバック(A/B)回路及び  
特別管理回路に使用する時に適用する事。

NOTES

1. MATERIAL : PBT
- COLOR : SEE TABLE
2. MATING PART NO. : 7282-1080 ETC., 7182-2410
3. HANDLING MANUAL NO. YPES-15-408
4. PART NUMBERS IN PARENTHESIS SHALL BE USED FOR  
AIR BAG (A/B) CIRCUITS AND OTHER CIRCUITS DESIGNATED  
FOR SPECIAL MONITORING.



| CHANGED PART NAME. ETC.               |  |  |  |  |  |  |  |  |  | C10-ZB28                            |  | K. K      |  | CUSTOMER    |  | CUSTOMER PART NO. |  | SPEC.     |  | SEE NOTES                              |  | MTRL.              |  | TREAT.      |  | ISSUE MARK     |  |
|---------------------------------------|--|--|--|--|--|--|--|--|--|-------------------------------------|--|-----------|--|-------------|--|-------------------|--|-----------|--|----------------------------------------|--|--------------------|--|-------------|--|----------------|--|
| ADDED COLOR PART NO. , ETC.           |  |  |  |  |  |  |  |  |  | C06-Z104                            |  | E. S      |  | CUSTOMER    |  | CUSTOMER PART NO. |  | SPEC.     |  | SEE NOTES                              |  | MTRL.              |  | TREAT.      |  | ISSUE MARK     |  |
| ADDED A/B PART NO.                    |  |  |  |  |  |  |  |  |  | C04-X070                            |  | S. N      |  | CUSTOMER    |  | CUSTOMER PART NO. |  | SPEC.     |  | SEE NOTES                              |  | MTRL.              |  | TREAT.      |  | ISSUE MARK     |  |
| NEW, [A]                              |  |  |  |  |  |  |  |  |  | C03-X492                            |  | E. F      |  | OFFICE      |  | TRIAL PART NO.    |  | NAME      |  | HLC 2. 3 II (090 II) 8P HOUSING FEMALE |  | MTRL.              |  | TREAT.      |  | ISSUE MARK     |  |
| REVISION RECORD                       |  |  |  |  |  |  |  |  |  | NO.                                 |  | CHKD      |  | VENDOR      |  | VENDOR NO.        |  | NAME      |  | HLC 2. 3 II (090 II) 8P HOUSING FEMALE |  | MTRL.              |  | TREAT.      |  | ISSUE MARK     |  |
| GENERAL TOLERANCE                     |  |  |  |  |  |  |  |  |  | ANGLE                               |  | ECCENT    |  | DNG TYPE    |  | DNG SOURCE        |  | DNG DATE  |  | UNIT                                   |  | SQI                |  | ANGLE       |  | PART NO.       |  |
| 10MAX 50MAX 100MAX 250MAX 250OVR      |  |  |  |  |  |  |  |  |  | ±0.15 ±0.2 ±0.3 ±0.5 ±0.75 ±30' 0.1 |  | R         |  | NEW         |  | 03/08/06          |  | mm        |  | 2:1                                    |  | 3                  |  | CH. CODE    |  | 7183-2510, [A] |  |
| A ±0.15 ±0.2 ±0.3 ±0.5 ±0.75 ±30' 0.1 |  |  |  |  |  |  |  |  |  |                                     |  |           |  | CHECKED     |  | DESIGN            |  | DRAWN     |  |                                        |  | DWG NO.            |  | SET DWG NO. |  |                |  |
| B ±0.2 ±0.3 ±0.55 ±0.95 ±1.4 ±30' 0.1 |  |  |  |  |  |  |  |  |  |                                     |  | APPROVED  |  | CHECKED     |  | K. KIDA           |  | E. FUKUDA |  | M. ALAGAR                              |  | 7183-2510:R        |  |             |  |                |  |
| C ±0.3 ±0.5 ±0.8 ±1.4 ±2 ±30' 0.15    |  |  |  |  |  |  |  |  |  |                                     |  | M. FUKUDA |  | O. SUGIYAMA |  | K. KIDA           |  | E. FUKUDA |  | M. ALAGAR                              |  | 7183-2510:R        |  |             |  |                |  |
| MASS                                  |  |  |  |  |  |  |  |  |  |                                     |  | 10/12/08  |  | 10/12/08    |  | 10/12/08          |  | 02/09/11  |  | 10/12/08                               |  | YAZAKI CORPORATION |  |             |  |                |  |
| SPECIFIED                             |  |  |  |  |  |  |  |  |  |                                     |  |           |  |             |  |                   |  |           |  |                                        |  |                    |  |             |  |                |  |