

1 2 3

SEC. A-A

SUB ASS'Y PART NO.	NO.	PART NAME	PART NO.	MATERIAL	COLOR
7222-4220-40	①	Y TYPE CONN. HSG. 2P FOR M-TM	7122-4220-40	PBT	LIGHT GRAY
	②	Y TYPE CONN. 2P PACKING	7137-2511-80	SILICONE RUBBER	RED-IRON
7222-4220-30	①	Y TYPE CONN. HSG. 2P FOR M-TM	7122-4220-30	PBT	BLACK
	②	Y TYPE CONN. 2P PACKING	7137-2511-80	SILICONE RUBBER	RED-IRON

NOTES

1. MATING PART NO. : 7123-4220-40 ETC.
2. APPLICABLE REAR HOLDER NO. : 7157-6800-80
3. APPLICABLE TERMINAL NO. : 7114-3250, 7114-3251
4. APPLICABLE RUBBER STOPPER NO. : 7157-3580-60, 7157-3581-80

注記

1. 嵌合相手品番 : 7123-4220-40 ETC.
2. 適用リヤホルダ品番 : 7157-6800-80
3. 適用端子品番 : 7114-3250, 7114-3251
4. 適用ゴム止り品番 : 7157-3580-60, 7157-3581-80

59.80

(33.00)
27.50
11.00
A
17.60
28.45
A
2
1
A

					CUSTOMER		MATL. SEE TABLE		TREAT.					
					CUSTOMER PART NO.	CUSTOMER DWG NO.	SPEC.		& FIN.					
▲	91.12.13	ADDED PART NO.	C91-L871	T.M			NAME Y TYPE CONNECTOR 2P SUB-		ASS'Y FOR MALE TERMINAL					
	89.05.15	N E W	C89-L618	S.K	OFFICE	STDLIB NO.								
LET	DATE	REVISION RECORD	NO.	CHKD	VENDOR									
GENERAL TOLERANCE					VENDOR NO.									
	10MAX	50MAX	100MAX	250MAX	250OVR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	PART NO.
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30°	0.1	R	NEW	89.05.23	mm	2/1	3	▲ 7222-4220-40 ETC.
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30°	0.1	APPROVED	CHECKED	CHECKED	DESIGN	DRAWN	DWG NO.	▲ 7222-4220-30-R
©	±0.3	±0.5	±0.8	±1.4	±2	±30°	0.15	H. Eto	Therji	S. KOZONO	ISHIZUKA	DWG NO. ▲ 7222-4220-30-R TRIAL PART NO.		
SPECIFIED					MASS		YAZAKI CORPORATION							