




A

B



SEC. A-A



SEC. B-B

TABLE 1

SUB ASSEMBLY PART NO. AND CH. CODE		NO.	PART NO. AND CH. CODE	MATERIAL	COLOR	QTY.
7282-1028 ETC.		①	SEE TABLE 2	HPA	SEE TABLE 2	1
		②	7157-4091 (7B57-4091)	HPA	NATURAL	1

TABLE 2

SUB ASSEMBLY PART NO. AND CH. CODE		PART NO. AND CH. CODE	COLOR
7282-1028, B		7182-1028	NATURAL
7282-1028-10, B		7182-1028-10	DARK GRAY
7282-1028-30, B		7182-1028-30	BLACK
7282-1028-40, B		7182-1028-40	LIGHT GRAY
7282-1028-90, B		7182-1028-90	BLUE

- 注記
- 嵌合端子品番: 7283-1028 ETC.
 - 適用端子品番: 7114-4020 ETC.
 - () 内品番はA/B回路及び特別電圧回路に使用すること。

NOTES

- MATING PART NO.: 7283-1028 ETC.
- APPLICABLE TERMINAL NO.: 7114-4020 ETC.
- PART NUMBERS IN PARENTHESIS SHALL BE USED FOR AIR BAG (A/B) CIRCUITS AND OTHER CIRCUITS DESIGNATED FOR SPECIAL MONITOR.

ISSUE MARK

△	99.01.07	ELIMINATED COLOR NO.			C98-N177	T.M	CUSTOMER				MATL. SPEC.	SEE TABLE 1	TREAT. & FIN.	
△	96.08.02	CHANGED FORM & CHANGED MATERIAL. 田			C96-M436	A.Y	CUSTOMER PART NO.							
	90.05.24	NEW			C90-L550	H.Y	OFFICE				NAME			
LET	DATE	REVISION RECORD			NO.	CHKD	VENDOR				SUB ASSEMBLY MALE			
GENERAL TOLERANCE														
	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	PART NO. CH. CODE
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1	R	NEW	90.05.23	mm	1/2	3	7282-1028 ETC. △(7C82-1028)
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1	APPROVED	CHECKED	CHECKED	DESIGN	DRAWN		DWG NO. 7282-1028:R
C	±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15	加藤 山梨 藤 幸			Y. OHTA	KANAZAWA	ヤザキ	SET DWG NO.
SPECIFIED						MASS		9		99.1.15	99.1.14	99.01.07	88.12.19	99.01.07
YAZAKI CORPORATION														

090II 2P CONNECTOR
SUB ASSEMBLY MALE

PART NO. 7282-1028 ETC. (7C82-1028)
CH. CODE 7282-1028:R
SET DWG NO.