




SUB ASSEMBLY PART NO.		PART NO.		MATERIAL		COLOR		QTY.	
AND CH. CODE		AND CH. CODE							
7282-8852-30, $\square/\Delta$		①		7182-8852-30		PBT		BLACK	
		②		Δ 7158-5263		PBT		Δ NATURAL	
								1	

NOTES

- MATING PART NO. : 7283-8852-30
- APPLICABLE TERMINAL NO. : 7114-4415-02 ETC.
- APPLICABLE SEAL RUBBER NO. : 7158-3165-90, 7158-3166-60, 7158-3167-80, 7158-3168-80
- APPLICABLE UNUSED CAVITY PLUG: 7158-3169-40

注記

- 嵌合相手品番 : 7283-8852-30
- 適用端子品番 : 7114-4415-02 ETC.
- 適用シール栓品番 : 7158-3165-90, 7158-3166-60, 7158-3167-80
7158-3168-80
- 適用防水栓品番 : 7158-3169-40



③	03/08/07	CHANGED CODE, C	C03-X324	T. Y	CUSTOMER					MATL. SPEC.	SEE TABLE	TREAT. & F. IN.									
②	02/12/04	CHANGED FORM, B	C02-Y493	T. Y	CUSTOMER PART NO.					NAME	RH TYPE CONNECTOR 3P	SUB ASSEMBLY MALE									
①	02/02/06	ELIMINATE SECTION, ETC.	C02-X199	T. Y																	
	01/11/08	NEW	C01-Y135	T. Y	OFFICE	TRIAL PART NO.															
LET	DATE	REVISION RECORD			NO.	VENDOR															
GENERAL TOLERANCE												VENDOR NO.									
	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	PART NO.	CH. CODE	SET DRW NO.					
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30°	O. 1	R	NEW	01/11/08	mm	2/1	3	7282-8852-30, 							
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30°	O. 1	APPROVED	CHECKED	CHECKED	DESIGN			7282-8852-30-R							
⑥	±0.3	±0.5	±0.8	±1.4	±2	±30°	O. 15				M. KASHIYAMA										
SPECIFIED						MASS				g		03.08.19		03/08/19		01/05/08		03/08/07		YAZAKI CORPORATION	