

8

A

(37.20)

YAZAKI SUB ASSEMBLY PART NO.	NO.	YAZAKI PART NO.	MATL. & SPEC.	COLOR	QTY.
7282-7023-10 ETC.	①	SEE TABLE 2	PBT	SEE TABLE 2	1
	②	7157-4102	PBT	NATURAL	1

TABLE 2		YAZAKI SUB ASSEMBLY PART NO.	YAZAKI PART NO.	COLOR
③		7282-7023	7182-7023	NATURAL
④		7282-7023-10	7182-7023-10	DARK GRAY
⑤		7282-7023-30	7182-7023-30	BLACK
⑥		7282-7023-40	7182-7023-40	LIGHT GRAY
⑦		7282-7023-50	7182-7023-50	ORANGE
⑧		7282-7023-60	7182-7023-60	GREEN
⑨		7282-7023-80	7182-7023-80	BROWN
⑩		7282-7023-90	7182-7023-90	BLUE

TABLE 2

SUB ASSEMBLY PART NO.		
7282-7023	A	7182-7023
7282-7023-10	A	7182-7023-10
7282-7023-30	A	7182-7023-30
7282-7023-40	A	7182-7023-40
7282-7023-50	A	7182-7023-50
7282-7023-60	A	7182-7023-60
7282-7023-80	A	7182-7023-80
7282-7023-90	A	7182-7023-90
		NATURAL
		DARK GRAY
		BLACK
		LIGHT GRAY
		ORANGE
		GREEN
		BROWN
		BLUE

NOTES

- 1) APPLICABLE TERMINAL NO. : 7114-4025 ETC.
- 2) MATING PART NO. : 7283-7023-10 ETC.
- 3) APPLICABLE RUBBER STOPPER NO. : 7158-3006-90 ETC.

陽

- 1) 適用鑄造品番 : 7114-4025 ETC.
- 2) 嵌合相手品番 : 7283-7023-10 ETC.
- 3) 適用工具品番 : 7158-3006-90 ETC.

A		97.06.06	CHANGED FORM & ADDED PART NO. .A		C97-L957	M. T
A		89.10.04	ADDED PART NO.		C89-M068	M. H
A		89.08.19	CHANGED FORM & RENEW		C89-L862	M. T
89.02.22		NEW			C89-L380	T. M
LET	DATE	REVISION RECORD		NO.	CHKD	
GENERAL TOLERANCE						
10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT
A ±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1
B ±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1
C ±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15
SPECIFIED					MASS	g

C97-L957		C97-L957		M. T	
C89-M068		C89-M068		M. H	
C89-L862		C89-L862		M. T	
C89-L380		C89-L380		T. M	
OFFICE		TRIAL PART NO.			
VENDOR		VENDOR NO.			
CUSTOMER		CUSTOMER PART NO.		CUSTOMER DWG NO.	
MATERIAL SPEC.		SEE TABLE 1		TREAT. & FIN.	
NAME 090II 2P SEALED CONNECTOR					
HOUSING MALE SUB ASSEMBLY					
PART NO.		CH. CODE		PART NO. A7282-7023-10 ETC.	
DWG NO.		DWG NO.		7282-7023-10:R	
SET DWG NO.		SET DWG NO.		YAZAKI CORPORATION	