






SUB ASSEMBLY PART NO. AND CH. CODE		NO.	PART NO. AND CH. CODE	PART NAME	MATERIAL	COLOR	QTY.
△7282-8851-30 ETC.		①	SEE TABLE 2	HOUSING	PBT	SEE TABLE 2	1
② △7158-5261			FRONT HOLDER			NATURAL	1
△TABLE 2 SUB ASSEMBLY PART NO. AND CH. CODE		SUB ASSEMBLY PART NO. AND CH. CODE		PART NO. AND CH. CODE	COLOR	MATING PART NO.	
		7282-8851-30, C		7182-8851-30	BLACK	7283-8851-30	
		7282-9392-40		7182-9392-40	LIGHT GRAY	7283-9392-40	
		7282-9393-10		7182-9393-10	DARK GRAY	7283-9393-10	
		7282-0528-80		7182-0528-80	BROWN	7283-0528-80	

注記

- 適用端子品番 : 7114-4415-02 ETC.
- 適用ゴム栓品番 : 7158-3165-90, 7158-3166-60, 7158-3182-20
7158-3167-80, 7158-3168-80
- 適用防水栓品番 : 7158-3169-40

NOTES

- APPLICABLE TERMINAL PART NO. : 7114-4415-02 ETC.
- APPLICABLE RUBBER SEAL PART NO. : 7158-3165-90, 7158-3166-60, 7158-3182-20
7158-3167-80, 7158-3168-80
- APPLICABLE UNUSED CAVITY PLUG PART NO. : 7158-3169-40



△/△ 7282-8851-30 (CODE A)	CHANGED PART NAME	C10-ZA94	R. E
△/△ 07/05/16	CORRECTION OF CLERICAL ERROR	C07-Z439	A. P
△/△ 06/10/12	ADDED PART NO., ETC.	C06-ZB09	M. A
△/△ 05/09/08	ADDED PART NO., ETC.	C05-ZC43	T. M
△/△ 03/08/07	CHANGED CODE, C	C03-X324	T. Y
△/△ 02/12/04	CHANGED FORM, B	C02-Y492	T. Y
△/△ 02/02/06	ELIMINATE SECTION, ETC.	C02-X199	T. Y
01/11/08	NEW	C01-Y135	T. Y
LET	DATE	REVISION RECORD	NO.
GENERAL TOLERANCE			
A	±0.15	50MAX 100MAX 250MAX	2500R
B	±0.2	±0.3 ±0.5 ±0.75	±30° O. 1
C	±0.3	±0.5 ±0.8 ±1.4	±30° O. 1
SPECIFIED			MASS

CUSTOMER		CUSTOMER PART NO.		CUSTOMER DWG NO.		MATERIAL		TREAT.		SPEC.		NAME		SUB ASSEMBLY MALE	
OFFICE		TRIAL PART NO.													
VENDOR NO.															
DWG TYPE		DWG SOURCE		DWG DATE		UNIT		SCL		ANGLE		PART NO.		PART NO.	
R		NEW		01/11/08		mm		2:1		3		CH. CODE		△7282-8851-30 ETC.	
APPROVED		CHECKED		DESIGN		DRAIN						DWG NO.		7282-8851-30:R	
S. MI ZUSE				R. CABANGAL		M. KASHIYAMA		R. ESPITAL							
10/11/15				10/11/15		01/05/08		10/11/15							

1

2

3