




SUB ASS'Y NO.	NO.	PART NO.	MATERIAL	COLOR	QTY.
7283-5538-40	①	7183-5538-40	HPA	LIGHT GRAY	1
	②	7158-4161	HPA	NATURAL	1

注 記

1. 嵌合相手品番: 7282-5538-40
2. 適用端子品番: 7116-4100-02 ETC.

NOTES

1. MATING PART NO. : 7282-5538-40
2. APPLICABLE TERMINAL PART NO. : 7116-4100-02 ETC.



△	98.01.30	CHANGED FORM. A	C97-M924	H. K	CUSTOMER	CUSTOMER PART NO.	CUSTOMER DWG NO.	MATL. SPEC.	SEE TABLE	TREAT. & FIN.	ISSUE MARK
△	96.02.23	CHANGED FORM & RENEW	C96-6173	K. O				NAME	1.5 SYSTEM CONNECTOR		
LET	DATE	REVISION RECORD	NO.	CHKD	OFFICE	TRIAL PART NO.			8P (F) SUB ASS'Y		
GENERAL TOLERANCE											
10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL ANGLE
A	±0.15	±0.2	±0.3	±0.5	±30'	0.1	R	NEW	95.07.13	mm	2/1 3
B	±0.2	±0.3	±0.55	±0.95	±1.4	0.1	APPROVED	CHECKED	CHECKED	DESIGN	DRAWN
(C)	±0.3	±0.5	±0.8	±1.4	±2	0.15	遠藤	角野	198.2.11	K. OHTAKA	SATOH
SPECIFIED											
PART NO. 7283-5538-40. A											
CH. CODE											
DWG NO. 7283-5538-40: R											
SET DWG NO.											
YAZAKI CORPORATION											