











△ CODE OVERVIEW

CODE A (SCALE 1:1)	CODE B (SCALE 1:1)	CODE C (SCALE 1:1)	CODE D (SCALE 1:1)	CODE O (SCALE 1:1)
 OPTION 1 28.00 ±0.20 23.30 ±0.20 24.15 ±0.20 0.85 ±0.10 4.85 ±0.20	 28.00 ±0.20 23.30 ±0.20 24.15 ±0.20 0.85 ±0.10 4.85 ±0.20	 28.00 ±0.20 23.30 ±0.20 24.15 ±0.20 0.85 ±0.10 4.85 ±0.20	 28.00 ±0.20 23.30 ±0.20 24.15 ±0.20 0.85 ±0.10 4.85 ±0.20	 28.00 ±0.20 23.30 ±0.20 24.15 ±0.20 0.85 ±0.10 4.85 ±0.20
P/N: 7298-6958-30, 7298-4285-30 COLOR: BLACK 9.5MM YPT WP CONNECTOR 1+1P (F) SUBASSEMBLY CODE A	P/N: 7289-7783-40 COLOR: GRAY 9.5MM YPT WP CONNECTOR 1+1P (F) SUBASSEMBLY CODE B	P/N:- COLOR: BLUE 9.5MM YPT WP CONNECTOR 1+1P (F) SUBASSEMBLY CODE C	P/N:- COLOR: BROWN 9.5MM YPT WP CONNECTOR 1+1P (F) SUBASSEMBLY CODE D	P/N:- COLOR: NATURAL 9.5MM YPT WP CONNECTOR 1+1P (F) SUBASSEMBLY CODE O

CODE A (SCALE 1:1)
 OPTION 2 (SEE NOTE 11) △ 14.00 ±0.20 11.65 ±0.20 24.15 ±0.20 0.85 ±0.10 4.85 ±0.20
P/N: 7287-8211-30 COLOR: BLACK 9.5MM YPT WP CONNECTOR 1+1P (F) SUBASSEMBLY CODE A




CONNECTION WITH COUNTER PART:
(SCALE 1:1)



NOTES:

1. MATERIAL: SEE TABLE;
2. COLOR: SEE TABLE;
- △3. FOR THE CORRECT MATERIAL SELECTION THE FINAL APPLICATION AND IT'S ATTACHMENT AREAS HAS TO BE CONSIDERED BY THE DESIGN OWNER. MATING PART SHALL HAVE THE SAME PLATING;
4. APPLICABLE TERMINALS: 7116-5625-02, 7116-5625-06;
5. APPLICABLE SEALS: 7158-3672-50 ETC.;
6. THIS DIMENSION SHOWS THE PRESET POSITION OF FRONT HOLDER ON THE SUBASSEMBLY;
7. MATING PRODUCT: ACCORDING DRAWING: 7287-8211-30A;
8. FOR GENERAL DIMENSIONAL AND POSITIONAL TOLERANCES SEE GENERAL TOLERANCE TABLE;
- △9. HANDLING MANUAL: YPES-15-1252;
10. PRODUCT STANDARD: N/A;
- △11. OPTION 2 NOT ADVISED TO BE USED WHEN MORE THAN ONE CODING IS REQUIRED;
12. THE MATERIALS USED IN THIS PRODUCT ARE IN CONFORMITY WITH REQUIREMENTS OF EU ELV 2000/53/EC DIRECTIVE AND ASSOCIATED DOCUMENTS.



△ 30.06.2021.	VIEWS AND NOTES UPDATED	Y21-0490	M.Z.
△ 23.11.2020.	NEW PART NUMBERS ADDED	Y20-0810	M.Z.
△ 09.10.2019.	NEW PART NUMBERS ADDED	Y19-0905	B.F.
△ 03.07.2018.	ADDED CODE (B) & UPDATED NOTES	Y18-0588	B.F.
04.04.2011.	NEW	Y11-0281	J.J.
LET	DATE	REVISION RECORD	NO.
			CHKD

GENERAL TOLERANCE							
	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1
○	±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15
SPECIFIED					MASS	23.5 g	

CUSTOMER						MATL. SPEC.		SEE NOTES		TREAT. & FIN.	
CUSTOMER PART NO.				CUSTOMER DWG NO.				NAME 9.5MM YPT WP CONNECTOR 1+1P (F) SUBASSEMBLY			
OFFICE YEL-P				TRIAL PART NO.							
VENDOR				X41019-E010							
VENDOR NO.											
DWG TYPE		DWG SOURCE		DWG DATE		UNIT	SCL	ANGLE			
R		NEW		04.04.2011.		mm	2:1	3			
APPROVED		CHECKED		CHECKED		DESIGN		DRAWN		PART NO.	
G.GREGURIC		B.FRETZE		M.POLGAR		B.FRETZE		M.ZOKALJ		CH. CODE 7287-8211-30 ETC.	
						18.01.2011.		30.06.2021.		DWG NO. 7287-8211-30:R	
										SET DWG NO.	
											