



1

2



3

STD LIB-SW2018

SUB ASSEMBLY PART NO. AND CH. CODE	NO.	PART NO.	PART NAME	MATERIAL	COLOR	QTY.
7297-1911-30	①	7197-1911-30	RH TYPE II 6P HOUSING MALE	△ PBT	BLACK	1
	②	7172-1618	RH TYPE II 6P FRONT HOLDER MALE	△ PBT	NATURAL	1



SEC. A-A



注記

1. かん合相手品番 : 7298-1869-30
2. 適用端子品番 : RH TYPE II TERMINAL
7195-1463-02 ETC. (TIN), 7195-1463-06 ETC. (SILVER)
RH TERMINAL
7114-4415-02 ETC. (TIN), 7114-4415-08 ETC. (GOLD)
RH TYPE II TERMINALを推奨する。
3. 適用ゴム栓品番 : 7158-3165-90 ETC. (TIN, GOLD), 7158-3166-10 ETC. (SILVER)
4. 適用防水栓品番 : 7158-3169-40

NOTES

1. MATING PART NO. : 7298-1869-30
2. APPLICABLE TERMINAL NO. : RH TYPE II TERMINAL
7195-1463-02 ETC. (TIN), 7195-1463-06 ETC. (SILVER)
RH TERMINAL
7114-4415-02 ETC. (TIN), 7114-4415-08 ETC. (GOLD)
RH TYPE II TERMINAL IS RECOMMENDED.
3. APPLICABLE SEAL RUBBER NO. : 7158-3165-90 ETC. (TIN, GOLD), 7158-3166-10 ETC. (SILVER)
4. APPLICABLE RUBBER STOPPER NO. : 7158-3169-40

GENERAL TOLERANCE											
	10 MAX	50 MAX	100 MAX	250 MAX	250 OVR	R5 MAX	R10 MAX	R20 MAX	R20 OVR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75					±3°	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4	±0.2	±0.3	±0.5	±2.5	±3°	0.1
◎	±0.3	±0.5	±0.8	±1.4	±2					±3°	0.15

△	2021/05/31	CORRECTION OF A CLERICAL ERROR		C21-P178	Y. M		
△	2021/03/03	ADDED APPLICABLE TERMINAL NO., ETC.		C21-P033	D. M		
	2020/02/17	NEW		C20-Y056	D. M		
LET	DATE	REVISION RECORD		NO.	CHKD		
GENERAL TOLERANCE							
	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±0.5°	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4	±1.0°	0.1
C	±0.3	±0.5	±0.8	±1.4	±2	±1.5°	0.15
SPECIFIED					MASS (4.8) g		

CUSTOMER						
CUSTOMER PART NO.						
CUSTOMER DWG NO.						
OFFICE				TRIAL PART NO. or PRODUCT NO.		
VENDOR						
VENDOR NO.						
DWG TYPE	DWG SOURCE		DWG DATE	UNIT	SCL	ANGL
R	NEW		2020/02/17	mm	2:1	3
APPROVED		CHECKED	CHECKED	DESIGN		DRAWN
S. NONAKA		Y. IWAHORI	———	Y. IWAHORI		Y. MAEDA
2021/05/31	2021/05/31	———	2018/02/15		2021/05/31	