





GENERAL TOLERANCE									
10 MAX	50 MAX	100 MAX	250 MAX	250 OVR	RS MAX	R10 MAX	R20 MAX	R20 OVR	ANGLE
A ± 0.15	± 0.2	± 0.3	± 0.5	± 0.75					ECCENT
B ± 0.2	± 0.3	± 0.55	± 0.95	± 1.4	± 0.2	± 0.3	± 0.5	± 2.5	$\pm 3^\circ$
C ± 0.3	± 0.5	± 0.8	± 1.4	± 2					$\pm 3^\circ$
									0.1
									0.1
									0.15

ASSEMBLY PART NO. AND CH. CODE	NO.	PART NO. AND CH. CODE	MATERIAL	COLOR	QTY.
7382-9454-30	①	7182-9454-30	PBT	BLACK	1
	②	7114-9518-02	BRASS TIN PLATING	—	2



SEC. A-A



- 注記
1. 嵌合相手品番 : 7283-2764-30 ETC.
 2. 適用クリップ品番 : 7147-8790

- NOTES
1. MATING PART NO. : 7283-2764-30 ETC.
 2. APPLICABLE CLIP PART NO. : 7147-8790

05/03/14		NEW		C05-7395		K. N		OFFICE		CUSTOMER PART NO.		CUSTOMER DWG NO.	
DATE		REVISION RECORD		NO.		CHKD		VENDOR		TRIAL PART NO.			
GENERAL TOLERANCE													
10MAX	50MAX	100MAX	250MAX	250OVR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	PART NO.
A ± 0.15	± 0.2	± 0.3	± 0.5	± 0.75	$\pm 30'$	0.1	R	NEW	05/03/14	mm	2:1	3	7382-9454-30
B ± 0.2	± 0.3	± 0.55	± 0.95	± 1.4	$\pm 30'$	0.1	APPROVED	CHECKED		DESIGN		DRAWN	7382-9454-30:R
C ± 0.3	± 0.5	± 0.8	± 1.4	± 2	$\pm 30'$	0.15	K. Okuma	K. Nishio	S. Matsui	K. Niiho		E. PANTONI	
SPECIFIED						MASS	8	205.03.14	05.03.14	05.03.14	05/02/17	05/03/14	
YAZAKI CORPORATION													

ISSUE MARK