



QBiP-1505A (MRZNR0S)

3.5" SubCompact Embedded Motherboard with AMD Ryzen™ R1505G Embedded Processor, Dual Channel DDR4 memory, 4 x COM, 1 x SATA 6Gb/s, 6 x USB



Specifications

Form Factor	3.5" SBC 146W x 101.7D mm
CPU	AMD Ryzen™ R1505G Embedded Processor 14nm, 2 cores, 4 threads, 2.4 GHz, up to 3.3 GHz TDP 25W
Socket	1 x FP5 type 1 BGA
Memory	2 x DDR4 SO-DIMM sockets, Max. Capacity 32 GB Support Dual channel DDR4 2400 MHz memory modules
Ethernet	2 x GbE LAN Ports (Realtek® RTL8111HS)
Video	Integrated Graphics Processor - AMD Radeon™ Vega 3 Graphics: 3 x HDMI 2.0 ports, supporting a maximum resolution of 4096x2160 @60Hz 1 x eDP port, supporting a maximum resolution of 3840x2160 @60Hz (Share from HDMI)
Audio	(3 independent display outputs) Realtek® Audio Codec

Features


- 3.5" SBC
- AMD Ryzen™ R1505G Embedded Processor
- Dual Channel DDR4, 2 x SO-DIMMs
- 2 x GbE LAN Ports
- 1 x SATA 6Gb/s Port
- M.2 with SATA 6Gb/s or PCIe Gen 3x4
- 3 x HDMI 2.0, eDP ports for multiple display
- 2 x COM Ports (RS-232/422/485 & RI/5V/12V)
- 2 x COM Ports (RS-232)

Storage	1 x SATA 6Gb/s Port
Expansion Slots	1 x 2280 M.2 M-Key (PCIe Gen 3x4, SATA 6Gb/s) 1 x 2230 M.2 E-Key 1 x Full-size Mini PCIe with SIM slot
Internal I/O	1 x 4-pin box power connector (DC in +9V~36VDC) 1 x SATA Power header 1 x CPU fan header 1 x System fan header 1 x Front panel header 1 x Front panel audio header 1 x 2W Speaker out header 4 x USB 2.0 headers 2 x COM headers (RS-232) 2 x COM headers (RS-232/422/485 & RI/5V/12V) 1 x Backlight Control header 1 x AT/ATX mode select jumper 1 x eDP/HDMI jumper 1 x GPIO (8-bits) & SMBus header 1 x Buzzer
Rear I/O	3 x HDMI 2 x RJ45 LAN Ports 2 x USB 3.2 Gen 1
TPM	Onboard TPM 2.0 security chip INFINEON SLB9665TT2.0
OS Compatibility	Windows 10 (x64)
Operating Properties	Operating temperature: 0°C to 60°C Operating humidity: 0-90% (non-condensing) Non-operating temperature: -40°C to +85°C Non-operating humidity: 0%-95% (non-condensing)
Packing Content	Carton size: 465 x 351 x 217 (mm) Packing Capacity: 10pcs Including: SATA power Cable x 1 (P/N: 25CRI-200B02-K1R)
Order Information	9MRZNR0SMR-SI (Box Packing)


GIGAIPC reserves the right to modify or change technical data without prior notice.

Dimension (Unit: mm)

2024/06/18



Block Diagram



Optional Kit

Part No.	Description	Quantity
12SF2-01A073-00R	Fansink	1
25ST1-113104-A7R	Fanless sink	1
25ST5-QP1600-A8R	Heat spreader	1

GIGAIPC reserves the right to modify or change technical data without prior notice.