




220-03 and 220-13 Solder Mount Bulkhead Receptacle

How To Order



Series No.	Class <i>H</i> = Hermetic	Insert Arrangement	Polarization (<i>N, 1, 2, 3, 4</i>)
220-03	H	24-61	P N
Shell Style <i>03</i> = Standard <i>13</i> = Scoop Proof		Shell Size <i>P</i> = Pins <i>S</i> = Sockets	

H



APPLICATION NOTES

1. Prior to use, lubricate O-rings with high grade silicone lubricant (Moly-kote M55 or equivalent).
2. Hermeticity rating: less than 1×10^{-6} cc helium per second.

Metric dimensions (mm) are indicated in parentheses

© 2013 Glenair, Inc.

U.S. CAGE Code 06324

Printed in U.S.A.

GLENAIR, INC. • 1211 AIR WAY • GLENDALE, CA 91201-2497 • 818-247-6000 • FAX 818-500-9912
www.glenair.com H-12 E-Mail: sales@glenair.com

220-03 and 220-13 Solder Mount Bulkhead Receptacle



Series 22 Geo-Marine
Connectors

H

Dimensions				
SHELL SIZE	B THREAD CLASS 2A	C DIA MAX	D DIA	E DIA $+.010+(0.3)$ $-.000-(0.0)$
10	.750 - .1P - .1L	.870 (22.1)	1.00 (25.4)	.875 (22.2)
12	.875 - .1P - .1L	.995 (25.3)	1.13 (28.7)	1.000 (25.4)
14	1.000 - .1P - .1L	1.120 (28.4)	1.25 (31.8)	1.125 (28.6)
16	1.125 - .1P - .1L	1.245 (31.6)	1.38 (35.1)	1.250 (31.8)
18	1.250 - .1P - .1L	1.370 (34.8)	1.50 (38.1)	1.375 (34.9)
20	1.375 - .1P - .1L	1.495 (38.0)	1.63 (41.4)	1.500 (38.1)
22	1.500 - .1P - .1L	1.620 (41.1)	1.75 (44.5)	1.625 (41.3)
24	1.625 - .1P - .1L	1.745 (44.3)	1.88 (47.8)	1.750 (44.5)

Replacement O-Ring Part Numbers *	
SHELL SIZE	PISTON O-RING
10	2-014
12	2-016
14	2-018
16	2-020
18	2-022
20	2-024
22	2-026
24	2-028
* Parker O-ring part numbers. Compound N674-70 or equivalent.	

Metric dimensions (mm) are indicated in parentheses