
EWM-C128F01E

Wide-Temp 4G CAT1, Full-size Mini PCle Card (with SIM holder)



Features

- 4G/LTE Bands Cat. 1
- DL:10 Mbps, UL:5 Mbps
- Operating temperature: -40 to +85 °C
- Build-in nano SIM card holder

ROHS COFFICE CE FCC

Specifications

Main Chipset	u-blox LARA-R280 4G LTE CAT1 engine
Antenna	2 LTE Antenna Coaxial Connectors
	4G/LTE Cat. 1:
Band	Bands 3, 8, 28 for Taiwan
	3G UMTS: band 1
Data throughput	4G/LTE Cat.1 (DL:10 Mbps, UL:5 Mbps)
Interface	USB 2.0
Operation Voltage	3.3V ~ 3.6V
O.S Supported	Windows, Linux, and Android
Temperature Ranges	Operation: -40 to +85 °C
Dimensions (L x W x H)	50.85 x 29.9 x 6.2 mm

Ordering Information

Part No.	Product Description
FWM-C128F01F	LTE/HSPA module with SIM Slot for Taiwan

Suggested Antenna and Cable

Part No.	Specifications
1750007990-01	4G/LTE full band dipole antenna, 110 mm
1750006264	Coaxial GSM/ GPS Cable, 150 mm
1750006009	Coaxial GSM/ GPS Cable, 250 mm
1750008303-01	4G/LTE full band dipole antenna 130 mm