



Connector Location A


Connector Location B




X
male




Loading Plan



Y
female



-Protection level: IP65/67
-Temperature range: -25°C ... +80°C



length in "1m" step	40	XXX=400
	39	XXX=390
	.	.
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	a [m]	XXX

4.0 to 40	±1%
0.1 to 3.9	+0.04
a [m]	Tolerance

Part no.	213478755XXXXX
----------	----------------

Dim. d[mm]	Type of cable	XX
Ø5.4	PVC grey, 5x0.25mm ²	XX=69
Ø5.6	PUR black, 5x0.34mm ²	XX=68

All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
All rights reserved		Created by STOCHECIC Stocbeci		Inspected by COSTEA Costea		Standardisation MUNTEANV Muntean	
Department HCS - RO		Date 2019-03-27		State Final Release		Doc-Key / ECM-Nr. 100677144/UGD/011/D 500000149491	
HARTING Customised Solutions		Title M12 Cab Assy shield A-cod st/st m/f		Rev. D		Page 1/1	
D-32339 Espelkamp		Type TB		Number 213478755XXXXX			