




Connector Location A

Connector Location B



- Protection level: IP67
- Temperature range: -30°C ... +60°C



4.0 to 100	±1%
0.1 to 3.9	+0.04
a [m]	Tolerance

length in "1m" step	100	XXX=000
	99	XXX=990
	.	.
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	a [m]	XXX

PVC violet, 2xAWG22	21348889486XXX
Type of cable	Part no.

 All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
	All rights reserved		Created by 407675 Lorinczi	Inspected by BANCUID Banciu	Standardisation MUNTEANV Muntean	Date 2024-02-12	State Final Release
	Department HCS - GPM		Title M12 Cable Assembly B-cod st/st m/f				Doc-Key / ECM-Nr. 100579391/UGD/009/C 500000253531
HARTING Customised Solutions D-32339 Espelkamp			Type TB	Number 21348889486XXX		Rev. C	Page 1/1