



Connector Location A

Connector Location B



Shield


1	white
2	brown
3	green
4	yellow
5	grey
6	pink
7	blue
8	red


length in "1m" step	100	XXX=000
	99	XXX=990
	.	.
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	a[m]	XXX

4.0 to 100	±1%
0.1 to 3.9	+0.04
a [m]	Tolerance

8x0.14mm², TPU, black	2134B200822XXX
Type of cable	Part no.

- Temperature range: -30°C...+80°C
- Protection level: IP67



		All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing 2016-08-22					
		All rights reserved		Created by POPESCUD		Inspected by POPESCUD		Standardisation MUNTEANV		Date 2016-08-24		State Final Release	
		Department HCS - RO											
HARTING Customised Solutions D-32427 Minden				Title M8 A-coded Cable Assembly								Doc-Key / ECM-Nr. 100686412/UGD/000/A 500000108011	
				Type TB		Number 2134B200822XXX						Rev. A	