




	1	2	3	4	5	6	7	8
A								
B								
C	27	33612211000003	Fiber optic, multi mode 62.5/125 µm	100				
	26	33612210900003		90				
	25	33612210800003		80				
	24	33612210700003		70				
	23	33612210600003		60				
	22	33612210500003		50				
D	21	33612210450003		45				
	20	33612210400003		40				
	19	33612210350003		35				
	18	33612210300003		30				
	17	33612210250003		25				
	16	33612210200003		20				
	15	33612210150003		15				
	14	33612210140003		14				
	13	33612210130003		13				
	12	33612210120003		12				
	11	33612210110003		11				
E	10	33612210100003		10				
	9	33612210090003		9				
	8	33612210080003		8				
	7	33612210070003		7				
	6	33612210060003		6				
	5	33612210050003		5				
	4	33612210040003		4				
	3	33612210030003		3				
	2	33612210020003		2				
F	1	33612210010003		1				
	Cont. no.	Part no.	Type of cable	Dim. a[m]				



HARTING Customised Solutions
D-32339 Espelkamp

All rights reserved
Department HCS - RO

Created by
COSTEA

Inspected by
COSTEA

Standardisation
MUNTEANV

Date
2018-07-19

State
Final Release

Title
FO CA PP2-PP2, 62.5µ, OM1, PUR

Type
TB

Number
3361221XXX0003

Doc-Key / ECM-Nr.
100677817/UGD/006/D
500000137829

Rev.
D

Page
2/2



All Dimensions
in mm

Tech. Character.

Free size tol.

According to production drawing